


- Stamped Rigging screw with eye and hook
- Fitting component
- Material: zinc plated steel Fe430B



Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3
- Not sold individually, please contact us for details



DISCOUNTS

Qty	1+	5+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØM	B	C	D	E	F	G	H	L1	L2	SLW (kg)	Weight (kg)	Price each
TAC1-05	M5	80	60	40	8	62	40	6	114	176	50	0,055	2,59 €
TAC1-06	M6	80	74	47	10	76	50	8	141	200	75	0,064	2,90 €
TAC1-08	M8	105	79	52	11	88	52	10	156	236	165	0,126	3,73 €
TAC1-10	M10	125	95	61	14	114	60	11	187	276	235	0,214	5,76 €
TAC1-12	M12	140	105	65	17	122	66	16	226	311	320	0,398	8,01 €
TAC1-14	M14	170	128	85	18	147	82	15	254	378	430	0,608	11,93 €
TAC1-16	M16	190	160	97	23	172	105	20	296	466	530	0,845	16,57 €

*Depending on availability - Dimensions in mm

Stainless steel rigging screw with hook/eye



Turnbuckle

TACss

- Rigging screw with eye and hook
- Fitting component
- Material: stainless steel 316

Info.

- SWL: safe working load.
- The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3



DISCOUNTS

Qty	1+	5+	10+	20+	30+
Disc. List	-5%	-10%	-15%	On request	

Part number	ØA	B	ØD	L1	L2	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
TAC1-05/SS	M5	9	8,3	71	122-179	180	0,046	✓	8,30 €
TAC1-06/SS	M6	9,5	10,0	90	160-228	360	0,076	✓	9,95 €
TAC1-08/SS	M8	11	12,0	120	210-303	650	0,165	✓	17,20 €
TAC1-10/SS	M10	13	15,8	150	255-376	1000	0,285	✓	21,96 €
TAC1-12/SS	M12	16,8	20,0	200	305-473	1400	0,515	-	33,67 €
TAC1-16/SS	M16	16,3	26,0	245	400-593	2300	1,110	-	68,29 €

*Depending on availability - Dimensions in mm

Rigging screw with 2 hooks

Stock Ste

TCC


Turnbuckle

- Stamped Rigging screw with two hooks
- Fitting component
- Material: zinc plated steel Fe430B



Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3
- ** Not sold individually, please contact us for details



DISCOUNTS

Qty	1+	5+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØM	B	C	D	E	L1	L2	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
TCC1-05	M5	80	62	40	6	116	178	50	0,052	✓	2,69 €
TCC1-06	M6	80	76	50	8	143	205	75	0,065	✓	2,98 €
TCC1-08	M8	105	88	52	10	165	245	165	0,136	✓	4,06 €
TCC1-10	M10	125	111	60	12	213	307	235	0,220	✓	6,20 €
TCC1-12	M12	140	130	66	15	252	350	320	0,420	-	8,12 €
TCC1-14	M14	170	147	86	15	277	407	420	0,640	-	13,28 €
TCC1-16	M16	190	172	105	20	298	463	530	0,880	-	17,63 €

*Depending on availability - Dimensions in mm

Stainless steel rigging screw with 2 hooks



Turnbuckle

TCCss

- Rigging screw with two hooks
- Fitting component
- Material:
Clamp : stainless steel 316

Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3



DISCOUNTS

Qty	1+	5+	10+	20+	30+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØA	B	L1	L2	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
TCC1-05/SS	M5	9	71	128-184	180	0,045	✓	8,30 €
TCC1-06/SS	M6	10	90	160-228	360	0,075	✓	9,95 €
TCC1-08/SS	M8	9	120	215-309	650	0,165	-	17,20 €
TCC1-10/SS	M10	12	150	265-380	1000	0,280	-	21,96 €
TCC1-12/SS	M12	15	200	310-480	1400	0,510	-	33,67 €
TCC1-16/SS	M16	16	243	400-594	2300	1,060	-	68,29 €

*Depending on availability - Dimensions in mm