


# Threaded lifting ring

WBGv  RUD® Base rotates through 360°

- Lifting ring for loads liable to swivel or tilt.
- Mounted on ball bearings
- Can be rotated under load
- Easy installation, only a tapped hole required
- Heavy duty lifting ring, manufactured and tested to DIN EN1677-4
- Surface finish: Pink epoxy powder over zinc plating
- Thread is 100% electromagnetically tested for cracks, CORRUD-DT coated
- Pivots through 180°





## Option


- Can be supplied with a longer thread and a mounting screw for use with a through hole or for mounting on lighter metals such as aluminium

## Info


- Conforms to EU Directive 98/37/CE




Nominal SWL  
Worst case lift  
direction



Aligned by  
hand, SWL  
increases



Vertical load  
SWL values doubled



Option:  
Extended thread,  
washer and nut




## DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List -3%	-6%	On request	

Part number	Load CMU(t)			ØM	A	B	C	D	E	F	G	SW	Weight (kg)	Price each	
	X	Y	Z												
WBG-V-M8	0,3	0,4	0,6	M8	8	31	29	30	76	13	102	36	27	0,18	102,28 €
WBG-V-M10	0,45	0,6	0,9	M10	8	31	29	33,5	78	17	122	38	30	0,29	108,02 €
WBG-V-M12	0,6	0,75	1,2	M12	10	49	35	42	107	21	140	47	36	0,41	114,79 €
WBG-V-M16	1,3	1,5	2,6	M16	13	46	38	48	114	25	180	56	41	0,59	123,10 €
WBG-V-M20	2	2,5	4	M20	13	54	35	62	137	33	223	67	55	1,42	206,79 €
WBG-V-M24	3,5	4,0	7	M24	18	66	40	81	173	40	255	88	70	2,63	277,98 €
WBG-V-M30	5	6,0	10	M30	22	90	50	99	221	50	330	106	85	5,09	370,98 €

\*Depending on availability - Dimensions in mm

## Our other products




PO

Pull handle - Multi-sector, Smooth hole



BFA

Shaft locking washer, E clip



CFC

Spring loaded position switch, Electric contact



CHMR75

Worm and wheel gear reducer, up to 298 Nm



LRX

Linear roller slide, Rail - from 9410 N to 101000 N



GRP2-14-A

Spring pin ISO8740, splined ISO 8740



AC156-157

Strike for toggle latch, 25.5mm



PRF\_FIX\_STD

Fastener for aluminium profile, Standard fastener



BH02

Single housed bearing assembly, Bearing



YG2

HEAVY DUTY spur gear, Steel 35NCD6



AT10-50ECO

AT type timing pulley, Economy range -



ZDB

Machined plastic bevel gear, 2:1

## Complementary products



VRSSs

Male swivelling lifting rings stainless steel, Male swivelling - ...



VRM

Female swivelling lifting rings, Female swivelling



PPS


Lifting ring, Universal threaded



VLBG

Lifting ring, Rotating


## Our other products



RPPM  
RPP type belt per metre, RPP8 Steel cored polyurethane



UGPC  
Actuator guide kit, Short bearing



BCM\_HPBT  
Modular cylindrical brush, PBT polyester bristles



SH1  
Parallel axis helical gear, Machined plastic (delrin)



PRES7HR  
Manual workbench press, Force up to 700kg



P20  
Worm and wheel gear reducer, up to 5 Nm



P30  
Worm and wheel gear reducer, up to 8.80 Nm




SH1  
Parallel axis helical gear, Steel 20NCD2



SHS  
Shoulder screw stainless steel 303, Stainless steel 303



MRA\_SS  
Stainless steel Quick link, Stainless steel



PRF\_JL5  
Lip seal for panel, Door seal - Ø 5mm



T10\_21\_AL  
T type timing pulley, Economy range - T10 aluminium

## Complementary products



VRSSs  
Male swivelling lifting rings stainless steel, Male swivelling - s...



VRM  
Female swivelling lifting rings, Female swivelling



PPS  
Lifting ring, Universal threaded



VLBG  
Lifting ring, Rotating