



DryLin®W bearing block






Size 16 - For loads of up to 2100N **WJUM16**

- Material:
Housing: Zamak
Liner: iglidur®j200

Advantages

- Full design flexibility using **WS16** single rails and **WJUM01-16** bearing blocks

Modular



DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Type	backlash	Max. static load (20°C) Weight (g)	Coy (N)	Coz+ (N)	Coz- (N)	Stock*	Price each 1 to 4
WJUM01-16	Fixed	0	100	2100	2100	400	✓	16,64 €
WJUM01-16-LL	Floating	±0,2	100	2100	2100	400	-	16,66 €

*Depending on availability - Dimensions in mm

Our other products



V3RA_PT

3-spoked handwheel with handle, Polyamide



PCS8ECO

Chain sprocket - steel, 8mm (DIN 05B-1)



DOG319

Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



PR40

Articulated foot Ø40, Ø 40



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



RPCpl

Swivel castor with double brake, Steel - Polyamide



BLH70

Right angled gearbox, from 26 to 128 Nm



PDM_PDV

Detectable plastic palm grip, by metal detectors



PPG

Indexing plunger with flange, With horizontal mounting



BAG

Steel Clamping collar, Steel



PW_PWG2

Worm - precision range, Stainless steel



CHMBR

Reaction arm, CHM and CHMR gear reducers reaction arm

Complementary products



WS16

Drylin® W rail, Rail



WW16

Drylin® W slide, slide assembly



WJRM

Drylin® W hybrid bearing block, Hybrid bearings