

Automatic chain tensioner

TC1RP

With 180° guide

- Tensioner for single chain

- Materials:

Housing: steel with corrosion proof epoxy finish


Profile: Green HD1000 polyethylene

Machined column: Black HD500 polyethylene



Screws and springs: stainless steel 304L

Adjustment

- Tension pressure can be reduced by freeing the springs, see instruction sheet



Detail A
Pre-tensioning spring



DISCOUNTS

Qty	1+	4+	10+
Disc.	List -10%	On request	

Part number	Chain	A	C	Stroke	Tension (N)			Price each
					1 spring	2 springs	3 springs	1 to 3
TC1-RP-06B1	06B1	5	30	40	60 to 132	120 to 264	180 to 396	232,34 €
TC1-RP-08B1	08B1	7	30	40	60 to 132	120 to 264	180 to 396	232,34 €
TC1-RP-10B1	10B1	9	30	40	60 to 132	120 to 264	180 to 396	232,34 €
TC1-RP-12B1	12B1	11	30	40	60 to 132	120 to 264	180 to 396	232,34 €

Dimensions in mm

Our other products



GSA_A
Adjustable gas spring,
Steel



PRFSRAD
Dual lock for
aluminium profile,
Quick fitting, self
locking door du...



M0
Worm and wheel set,
Unhardened steel



PCS37
Chain sprocket - steel,
9.525mm (DIN06B-1)



BABTss
303 Stainless steel
ball pin, 303 Stainless
steel



STRIP
Sealing brush strip,
3m length



CHAEpac
Square decorative
screwed hinges,
carbon fibre
reinforced



PAP
Handle for aluminium
profile, Ergonomic
handle




PRF4545
Standard stainless
steel pin profile, 45 x 45
mm



NPTF20
Fixed tube carrier,
Fixed Ø10 to Ø14



CHA35
Hinge for aluminium
profile, Hinge




RPPM
RPP type belt per
metre, RPP14 Steel
cored polyurethane

Complementary products



SUA4
Single chain supplied
by the metre, Steel



SBS_M
Single chain supplied
by the metre,
Stainless steel



TCXR
Automatic chain
tensioner, With steel
sprocket



RLR
Roll-Ring® chain
tensioner, Roll-Ring®
Self-adjusting