



## TKUU Compensates for any flexing of the shaft

- Self aligning closed linear bearing
- Compensates for any alignment errors or flexing of the shaft
- Integral seals
- Materials:  
 Bearing: Thermoplastic  
 Balls: Steel 70 HRC<sup>2</sup>



### Accessories

- Z-A and Z-B hardened and ground shafts
- NSB and S2B housings



Until  
**-20%\*\***

### DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-6%	-12%	On request

Part number	dr	D	L	W	D1	h	F	J	G	B	Loads		Stock*	Price each 1 to 4
											Dyn. C (N)	Stat. Co (N)		
TK-12-UU	12	22	32	1,30	21,00	-	3	0,7	-	22,9	1020	1290	✓	21,44 €
TK-16-UU	16	26	36	1,30	24,90	-	3	0,7	-	24,9	1250	1550	✓	26,31 €
TK-20-UU	20	32	45	1,60	30,30	-	3	0,9	-	31,5	2090	2630	✓	34,10 €
TK-25-UU	25	40	58	1,85	37,50	-	3	1,4	1,5	44,1	3780	4720	✓	44,82 €
TK-30-UU	30	47	68	1,85	44,50	-	3	2,2	2,0	52,1	5470	6810	✓	61,39 €
TK-40-UU	40	62	80	2,15	59,00	-	3	2,7	1,5	60,6	6590	8230	✓	93,85 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF\_BM  
Base support plate for aluminium profile,  
Central base fixation



MPS  
Hexagonal spacer,  
Stainless steel 303



BS2  
Panamech, Multi-Beam, Aluminium -  
with set screw



BLHT60  
Right angled gearbox,  
from 26 to 70 Nm



RFV63  
Stainless steel worm  
and wheel gearbox,  
up to 152 Nm



CHINV2  
Invisible hinge,  
Invisible - Opening up  
to 125°



PLS  
Cylindrical spacer,  
Stainless steel 303



TBL  
Mini leadscrew table  
with metric thread,  
1kg



DEP  
Tools Hygienic Usit®  
and Hygienic



BLHT30  
Right angled gearbox,  
from 1.65 to 4.40 Nm



T2,5-BAR  
T type tooth bar  
stock, T2.5



SSB  
Stainless steel bevel  
gear, 1:1

## Complementary products



ZA  
Shaft for linear  
guides, Hardened  
ground steel



ZB  
Shaft for linear  
guides, Hardened  
ground stainless steel



ZA  
Shaft for linear  
guides, Hardened  
ground steel