



## TKUU Compensates for any flexing of the shaft

- Self aligning closed linear bearing
- Compensates for any alignment errors or flexing of the shaft
- Integral seals
- Materials:  
 Bearing: Thermoplastic  
 Balls: Steel 70 HRC<sup>2</sup>



### Accessories

- Z-A and Z-B hardened and ground shafts
- NSB and S2B housings



Until  
**-20%\*\***

### DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-6%	-12%	On request

Part number	dr	D	L	W	D1	h	F	J	G	B	Loads		Price each 1 to 4	
											Dyn. C (N)	Stat. Co (N)		
TK-12-UU	12	22	32	1,30	21,00	-	3	0,7	-	22,9	1020	1290	✓	21,44 €
TK-16-UU	16	26	36	1,30	24,90	-	3	0,7	-	24,9	1250	1550	✓	26,31 €
TK-20-UU	20	32	45	1,60	30,30	-	3	0,9	-	31,5	2090	2630	✓	34,10 €
TK-25-UU	25	40	58	1,85	37,50	-	3	1,4	1,5	44,1	3780	4720	✓	44,82 €
TK-30-UU	30	47	68	1,85	44,50	-	3	2,2	2,0	52,1	5470	6810	✓	61,39 €
TK-40-UU	40	62	80	2,15	59,00	-	3	2,7	1,5	60,6	6590	8230	✓	93,85 €

\*Depending on availability - Dimensions in mm

## Our other products



VB

Small 6 lobe threaded handle - female, Duroplast - Stainless steel



T10\_21\_AL

T type timing pulley, Economy range - T10 aluminium



NKXR

Combined bearing without inner ring, Needle and cylindrical rollers



SCA

Flat cable clamp, Steel



GCA

Linch pin, Linch



GBMf

Flanged leadscrew nut, Flanged nut - Multiple starts



PTA50

Articulated levelling foot, pressed base Ø50, Ø 50




PM2

Worm and wheel set, Machined plastic (delrin)



TFR

Rigid manual tensioner, Fixed



INO

Internal gear, Machined plastic (delrin)



CLB\_M

Die cast zinc clamping lever - female, Zamak



RURt

Swivel castor with central hole, Polyurethane - Aluminium rim (Free ...

## Complementary products



ZA

Shaft for linear guides, Hardened ground steel



ZB

Shaft for linear guides, Hardened ground stainless steel



ZA

Shaft for linear guides, Hardened ground steel