

Rotating bent lever

New

GT64
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


Info

- The approximate fitting size: X = 32,7 mm for a tension of about 60 daN.
- Usable hook: AC161

NEW!



Application example



DISCOUNTS

| Qty | 1+ | 10+ | 20+ | 50+ |
|-------------|----|-----|-----|------------|
| Disc. Price | | -3% | -5% | On request |

| Part number | Material | Thickness latching tab | Thickness retaining bracket | Max. Stroke | Max. tension (daN) | Weight (g) | Price each 1 to 9 |
|-------------------|---------------------------|------------------------|-----------------------------|-------------|--------------------|------------|-------------------|
| Bent lever | | | | | | | |
| GT64-ZB | White galvanised steel | 15/10è | 12/10è | 6 | 80 | 39 | 8,12 € |
| GT64-SS | Rough 303 stainless steel | 15/10è | 12/10è | 6 | 80 | 39 | 10,12 € |
| Hook | | | | | | | |
| AC161-ZB | White galvanised steel | 15/10è | 12/10è | - | - | 3,7 | 0,29 € |
| AC161-SS | Rough 303 stainless steel | 15/10è | 12/10è | - | - | 3,7 | 0,39 € |

Dimensions in mm

New

Rotating bent lever with spring

Increased fitting tolerances

GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:



White galvanised steel or stainless steel

Advantage

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4$ mm for a tension of about 60 daN.
- Usable hook: **AC161**

**GT64R****AC161**

DISCOUNTS

| Qty | 1+ | 10+ | 20+ | 50+ |
|-------|-------|-----|-----|------------|
| Disc. | Price | -3% | -5% | On request |

| Part number | Material | Thickness latching tab | Thickness retaining bracket | Max. tension Stroke | Weight (daN) | Weight (g) | Price each 1 to 9 |
|-------------------|---------------------------|------------------------|-----------------------------|---------------------|--------------|------------|-------------------|
| Bent lever | | | | | | | |
| GT64R-ZB | White galvanised steel | 15/10è | 20/10è | 6 | 80 | 39 | 10,93 € |
| GT64R-SS | Rough 303 stainless steel | 15/10è | 20/10è | 6 | 80 | 39 | 13,27 € |
| Hook | | | | | | | |
| AC161-ZB | White galvanised steel | 15/10è | 20/10è | - | - | 3,7 | 0,29 € |
| AC161-SS | Rough 303 stainless steel | 15/10è | 20/10è | - | - | 3,7 | 0,39 € |

Dimensions in mm

Our other products



LBE

Miniature closed linear bearing, Miniature



PGNT

Thermoplastic T handle, With threaded insert



BABpss

301 Stainless steel ball pin, Stainless steel



WJUM20

Drylin® W bearing block, Slide



DOMI120

Domino 120 adjustable slide, Slide DOMILINE 120



NT121

Spur gear coaxial gearbox, from 20 to 68 Nm - Inline



PTA80ssEB

Articulated foot with sheet metal base Ø80, Articulated foot



LACM_SS

Stainless steel cam lever, Female



M2

Worm and wheel set, Machined plastic (delrin)



PRF_FIX_ANG

Fastener for aluminium profile, Angular joint



SF_ZZ

Deep groove ball bearing, Stainless steel



BPTR_M

End cap with threaded insert for round tube, With threaded insert

Complementary products



gt64r

Rotating bent lever with spring, Increased fitting tolerances