

# Fixed castor for aluminium profile

## TPEF

### For loads up to 120kg

- Castor for aluminium profil 40/45mm  
such as PRF4545

- Materials:

Plate: powder-coated steel sheet,  
natural aluminium colour

Wheel: grey polypropylene (RAL 7001)

### Advantages


- Silent
- Will not mark floor
- Low rolling resistance

### Info

- Fixing screws not supplied  
(See PRF-ECL-M8 and BHC8/CHC8 screws)



Typical application



### DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/F	80	111	1000	484	22.58 €
TPE100/F	100	136	1100	577	27.13 €
TPE125/F	125	161	1200	675	30.39 €

Dimensions in mm

**HPC**

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



SBF

Sealed flange bearing unit for Food Industry, cover



AWMP

Aluminium shaft for linear guide, Aluminium



PW\_PWG2

Worm - precision range, Steel




DP

Dowel pin, Solid ISO 2338



MAC

Carabiner DIN5299 steel, Steel



TSM T10M

T type timing belt per metre, T10 Steel cored polyurethane



MDB\_MTB

Moulded plastic bevel gear (nylon), 3:1



CHM30-MOT

Asynchronous AC motorgearboxes 0.09 to 0.22kW, 0.09 to 0.22kW



BTCW

Cap for square tube to be welded, To be



LVT

Miniature motorised actuator 2A, 2 amperes



CABPVC

PVC covered galvanised steel



RCX-6

Spherical tilt washer - DIN6319, concave

## Complementary products

transparen...



TPEpbd

Castor for aluminium profile, Swivel with brake



PRF4545

Standard aluminium profile, 45 x 45 mm



PRF\_ECL

Nut for aluminium profile, Steel square nut with tab



BHC

Socket head button screw, Stainless steel A2