

Rotating bent lever

New

GT64
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


Info

- The approximate fitting size: $X = 32,7 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**

NEW!



Application example



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

HPC

WEB
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Increased fitting tolerances

GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:


White galvanised steel or stainless steel

Advantage


- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**



GT64R



AC161

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm


Our other products



Stainless steel
gearbox - accessories,
Mounting bracket



Spur gear coaxial
gearbox, from 10 to
35 Nm - Inline



Bearing block for
leadscrew, Fixed
Drylin® bearing block



Surface mounting
plate, Surface
mounting plate for
ball joint



Eco. range steel bevel
gear, 1:1



Flanged sintered
bronze bush, Self-
lubricating sintered
bronze



Flat suction cup,
silicon



Axle for tensioner
pulley, Shaft



Stainless steel bevel
gear, 1:1



Panel mounting block
for aluminium
structures, Support



Chain sprocket -
Stainless steel,
15.875mm (DIN)



Stainless steel rigging
screw (hook/eye),
Stainless steel

Complementary products



Rotating bent lever
with spring, Increased
fitting tolerances