

Rotating bent lever


New

GT64 AC161


Common applications

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:
White galvanised steel or stainless steel


NEW !



GT64



AC161



Application example

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension	Weight (daN)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

Increased fitting tolerances

**GT64R
AC161**

- **Closure by eccentric cam by turning the butterfly nut**
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:
White galvanised steel or stainless steel





Advantage

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4$ mm for a tension of about 60 daN.
- Usable hook: **AC161**



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness	Thickness	Max.			Price each
		latching tab	retaining bracket	Stroke	tension (daN)	Weight (g)	
Bent lever							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm

Our other products




BPPE

Ball transfer unit push fit, Light



CCL

Standard wire thimble, Steel



TBV

Manual lifting tables, 20kg



TIFbout

Threaded stud - DIN976A, Steel



PLM-C

Flat gripping magnet, Flat holding magnet



HW_HT

Half-rail guide, Rail



HW_HT

Half-rail guide, Wheel



BLOC

Doorstop, Doorstop




DOM150

Accessories, Clamping lever



VTSM

Ball head screws
Hygienic Design®,
Stainless steel



LAT1

1A motorised linear
actuator, 1 ampere



CHB

Reaction arm, CHB
gear reducers
reaction arm

Complementary products



gt64r

Rotating bent lever
with spring, Increased
fitting tolerances