

Rotating bent lever

New

GT64
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


Info

- The approximate fitting size: $X = 32,7 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: AC161

NEW!



Application example



GT64

AC161

DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

New

Rotating bent lever with spring

Increased fitting tolerances

GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:



White galvanised steel or stainless steel

Advantage

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**

**GT64R****AC161**

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm

Our other products



SUA4_L

Chain link, Steel



PSG15

Spur gear - precision range, Pre-hardened Steel 35NCD6



LWH

High rigidity linear slide, Rail - from 9320 N to 71300 N



BLH60

Right angled gearbox, from 19 to 70 Nm



T10-BAR

T type tooth bar stock, T10



GAL22

Conveyor wheel, Zinc plated steel




PLA

Flat magnet, Flat magnet



RAG

Roller guide,



STL

Guidance brush - Brush, Brush



DOMI30

Accessories, Fixing kit



CPAS-H

Folding bracket, For heavy loads



TCL-ECL

Support rod for heavy loads, Support spindle

Complementary products



gt64r

Rotating bent lever with spring, Increased fitting tolerances