


# H Type guide units



## UGH40

For **Ø32** actuators  
ISO 15552 (VDMA 24562)


- Guide system for standard pneumatic actuators
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling supplied
- Fixing holes conform to CNOMO standards
- Supplied with 4 fixing screws for actuator
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section



**Accurate even for long strokes**

### Material

- Body + face plate: anodised aluminium
- Couplings + screws: Zinc plated steel
- Guide shafts: Chromed steel



Attach cylinder using 4 off M6 screws on  $\geq 38$


### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator Ø (mm)	Guide rod Ø (mm)	Weight (kg)	Price each
UGH40-25	25	40	16	2,38	263,22 €
UGH40-50	50	40	16	2,46	264,90 €
UGH40-100	100	40	16	2,61	268,29 €
UGH40-160	160	40	16	2,80	272,39 €
UGH40-200	200	40	16	2,92	275,06 €
UGH40-250	250	40	16	3,08	278,48 €
UGH40-320	320	40	16	3,29	283,19 €
UGH40-400	400	40	16	3,54	288,61 €
UGH40-500	500	40	16	3,85	295,39 €
UGH40-600	600	40	16	4,16	302,21 €

Dimensions in mm

## Our other products




CAB

Stainless steel cable,  
Stainless steel



DILC

Indexing plunger with  
cam, with cam



B

Steel bevel gear, 1:1



PRF-SRA

Lock for aluminium  
profile, Lock



MDPOT

Potentiometer,



T39\_T49

Extension spring in  
metre length stainless  
steel, by the metre



UTKswcr

Utilitrak® 3 wheels  
carriage, Steel roller  
carriage



SBF

Sealed flange bearing  
unit for Food Industry,  
cover



RDS

Safety washer  
Hygienic Usit®,  
Stainless steel



PCS50

Chain sprocket - steel,  
12.7mm (DIN08B-1)



SVT20

Screwjack with  
travelling screw, with  
translating screw



PRF19\_E

Bracket for aluminium  
profile, PRF19 to  
PRF45

**Complementary products**