

Rotating bent lever


New

GT64 AC161


Common applications

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:
White galvanised steel or stainless steel


NEW !



GT64



AC161



Application example

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

Increased fitting tolerances

GT64R
AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel



NEW!

**Advantage**

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: X = 31,4 mm for a tension of about 60 dAN.
- Usable hook: AC161

**DISCOUNTS**

Qty	1+	10+	20+	50+
Disc.	-3%	-5%		On request
Price				

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (dAN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64R-ZB	White galvanised steel	15/10 \ddot{e}	20/10 \ddot{e}	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10 \ddot{e}	20/10 \ddot{e}	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10 \ddot{e}	20/10 \ddot{e}	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10 \ddot{e}	20/10 \ddot{e}	-	-	3,7	0,39 €

Dimensions in mm

Our other products



CHB

Double output shaft,
For CHB gearbox



ABL100005

Antistatic brush,
Standard



LSAG

Sleeve for splined ball
shaft, Chariot - from
514 N to 15386 N



BAC105

Storage bin, 8mm




DOG111

Motor-gearbox 12V
and 24V DC, from 1.5
to 6 Nm



PITA

Locking bolt, with T
handle



PRF_JL2

Lip seal for panel,
Door seal - Ø 2mm



PRF_VTM

Hammerhead screw,
Hammerhead screw



Q6

Deep groove ball
bearing, Steel



HTD8M-BAR

HTD type tooth bar
stock, HTD8



PSG055

Spur gear - precision
range, Stainless steel
316



UCFL_PBT

Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel

Complementary products



gt64

Rotating bent lever,
Common applications