

Turn-to-open bent lever



GT64 AC161

Common applications


- Closure by eccentric cam by turning the butterfly handle
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:
White galvanised steel or stainless steel

Info

- The approximate fitting size: $X = 32,7 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**



Typical application



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Turn-to-open draw latch							
GT64-ZB	White galvanised steel	15/10	12/10	6	80	39	11,55 €
GT64-SS	Rough 303 stainless steel	15/10	12/10	6	80	39	13,94 €
Hook							
AC161-ZB	White galvanised steel	15/10	12/10	-	-	3,7	0,32 €
AC161-SS	Rough 303 stainless steel	15/10	12/10	-	-	3,7	0,49 €

Dimensions in mm

Turn-to-open bent lever **with spring**

Increased fitting tolerances

GT64R
AC161

- Closure by eccentric cam by turning the butterfly handle
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:


White galvanised steel or stainless steel

Advantage


- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**



GT64R



AC161

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. Stroke	tension (daN)	Weight (g)	Price each 1 to 9
Turn-to-open draw latch							
GT64R-ZB	White galvanised steel	15/10	20/10	6	80	39	13,49 €
GT64R-SS	Rough 303 stainless steel	15/10	20/10	6	80	39	16,38 €
Hook							
AC161-ZB	White galvanised steel	15/10	20/10	-	-	3,7	0,32 €
AC161-SS	Rough 303 stainless steel	15/10	20/10	-	-	3,7	0,49 €

Dimensions in mm