


- Used with UTK-SWC Series V wheel carriage assemblies
- Carbon bearing steel with hardened steel raceways
- Running surface smooth to Ra 0.8µm
- Tolerance on length +/-2mm

Option

- Increased length, max 3600mm


DISCOUNTS

Qty	1+	2+	4+
Disc.	List -10%		On request

Part number	H	J	K	L	M	N Ø x depth (counterbore)	T (Ø hole)	P	Rail weight (kg/m)	Carriage weight (g)	Stock*	Price each
UTK1-SWR	15,0	4,0	26	1000	20	9,8 x 2,8	5,8	80	1,46	114	✓	265,96 €
UTK2-SWR	19,7	4,5	40	1000	20	14,3 x 3	8,8	80	2,70	330	-	340,52 €
UTK3-SWR	30,0	8,0	58	1000	20	14,3 x 5	8,8	80	5,91	943	-	504,66 €

*Depending of availability - Dimensions in mm

Our other products



BL8

Right angled gearbox, from 0.20 to 2 Nm



PAM_SS

Stainless steel articulated levelling foot, \varnothing 30 & 40




ZG2

Plastic spur gear, Machined plastic (delrin)



AZY_SS

Stainless steel cylindrical elasto mount, Stainless steel



NK80

Drylin®N miniature guiding system, Width 80mm



TBD

Manual leadscrew table with opposing threads, 2kg



ADL_M

Male eye bolt conforms to DIN580, Steel



BOX-CSss

Hose clamp, Box set of stainless steel hose clamps



SVR15

Screwjack with travelling nut, with



ACL-APB

Closing system for aluminium profile,



PRES

Manual workbench press accessory for



QTR

Tapered roller bearing, Steel

Complementary products



UTKswc

Utilitrak® 3 wheels carriage, Series V precision steel wheel



UTKswrr

V shaped channel Utilitrak®, V rail



UTKswc

Utilitrak® 3 wheels carriage, Series V precision steel wheel