


- Used with UTK-SWC Series V wheel carriage assemblies
- Carbon bearing steel with hardened steel raceways
- Running surface smooth to Ra 0.8µm
- Tolerance on length +/-2mm

Option

- Increased length, max 3600mm



DISCOUNTS

Qty	1+	2+	4+
Disc.	List -10%		On request

Part number	H	J	K	L	M	N Ø x depth (counterbore)	T (Ø hole)	P	Rail weight (kg/m)	Carriage weight (g)	Stock*	Price each
UTK1-SWR	15,0	4,0	26	1000	20	9,8 x 2,8	5,8	80	1,46	114	✓	265,96 €
UTK2-SWR	19,7	4,5	40	1000	20	14,3 x 3	8,8	80	2,70	330	-	340,52 €
UTK3-SWR	30,0	8,0	58	1000	20	14,3 x 5	8,8	80	5,91	943	-	504,66 €

*Depending of availability - Dimensions in mm

Our other products




RPPM
RPP type belt per metre, RPP8 Steel cored polyurethane



EX
Optional shaft for E-type gear reducers, E Gearboxes double sided ou...



PPCcss
Pad eye on mounting plate squarred, Stainless steel



KS
Keysteel, Steel - Keystock



gt64r
Rotating bent lever with spring, Increased fitting tolerances



BEAB
Knob star grip antibacterial, Star, anti-bacterial



EPRC
High helix leadscrew, Cylindrical nut - up to 40mm per rotation



ACLEPP
Right angled bracket for aluminium profile, 8 holes



YG4
HEAVY DUTY spur gear, Steel 35NCD6



PR125rehausse
Extension for articulated foot Ø123,



ZBRA
Machined plastic bevel gear , 1:1



BAN
Angular clamp, Adjustable

Complementary products



UTKswc
Utilitrak® 3 wheels carriage, Series V precision steel wheel



UTKswrr
V shaped channel UtiliTrak®, V rail



UTKswc
Utilitrak® 3 wheels carriage, Series V precision steel wheel