


- Used with UTK-SWC Series V wheel carriage assemblies
- Carbon bearing steel with hardened steel raceways
- Running surface smooth to Ra 0.8µm
- Tolerance on length +/-2mm

Option

- Increased length, max 3600mm


DISCOUNTS

Qty	1+	2+	4+
Disc.	List -10%		On request

Part number	H	J	K	L	M	N Ø x depth (counterbore)	T (Ø hole)	P	Rail weight (kg/m)	Carriage weight (g)	Stock*	Price each
UTK1-SWR	15,0	4,0	26	1000	20	9,8 x 2,8	5,8	80	1,46	114	✓	265,96 €
UTK2-SWR	19,7	4,5	40	1000	20	14,3 x 3	8,8	80	2,70	330	-	340,52 €
UTK3-SWR	30,0	8,0	58	1000	20	14,3 x 5	8,8	80	5,91	943	-	504,66 €

*Depending of availability - Dimensions in mm

Our other products



BLH30

Right angled gearbox, from 1.32 to 4.40 Nm



CLB_M

Die cast zinc clamping lever - female, Zamak



BPPE

Ball transfer unit push fit, Light



PTA150

Articulated levelling foot, pressed base Ø150, Ø 150




BDPR

Holding arm, Rigid



NPTF30

Spacer for tube carrier, Fixing accessory Ø14 to Ø20



EZYSS

Stainless steel cylindrical stop, stainless steel



MDB_MTB

Moulded plastic bevel gear (nylon), 2:1



PWC

Powercoil thread inserts, Kit Powercoil -



ACM_DZ

Clip for bonnet fastener, Clip



FB_ECO

Eco. range steel bevel gear, 4:1



STU

Stroke rotary bushing, Steel

Complementary products



UTKswc

Utilitrak® 3 wheels carriage, Series V precision steel wheel



UTKswrr

V shaped channel UtiliTrak®, V rail



UTKswc

Utilitrak® 3 wheels carriage, Series V precision steel wheel