



- **AlNico magnets with central through drilled mounting hole**



- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

For recessed mounting, following precautions should be observed

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...




DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc. List	-15%	-20%	-30%	On request	

Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

*Depending on availability - Dimensions in mm

Our other products



T5M T10M
T type timing belt per
metre, T10 Steel
cored polyurethane



PAP
Handle for aluminium
profile, Ergonomic
handle



VTHbr
Hexagonal headed
screw VTH - DIN933,
Brass



PM4
Worm and wheel set,
Bronze



T39_T49
Extension spring in
metre length steel, by
the metre



FBL6000_K1
Brush strip per meter
PA6 fibres Ø0.2 to
Ø0.3, Black polyamide
6 ...



ERF
Quick fitting threaded
cable terminal, Cable
terminal with
threaded ...



CMM
Male rod ends DIN
ISO12240-4, Steel /
bronze



GLB
Small 6 lobe female
handle,



UCF_PBT
Stainless
steel/Polymer flanged



SH2
Parallel axis helical
gear, Machined plastic



PO
Pull handle - Multi-
sector, Smooth hole

Complementary products



PLC_PLT
Magnetic stud with
central hole, With
central hole



PLC_PLT
Magnetic stud with
threaded hole, With
threaded hole