



Magnetic stud with central hole

AlNiCo

VAP



- AlNiCo magnets with central through drilled mounting hole
- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

For recessed mounting, following precautions should be observed

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

*Depending on availability - Dimensions in mm


Our other products



PR530
Stainless steel articulated foot $\varnothing 30$, $\varnothing 30$



INS_SS
Self tapping stainless steel insert, Stainless steel



RPPM
RPP type belt per metre, RPP5 Steel cored polyurethane



RPCpl
Fixed castor with plate, Steel - Polyamide



SHA
Handwheel without handle, Polyamide



CHINV2
Invisible hinge, Invisible - Opening up to 125°



SDC
Positioning sleeve for indexing pin, For pin $\varnothing 4$ to $\varnothing 12$




OPFL_OPPM
Numerical counter accessories, Locking clamp



ACL-APB
Closing system for aluminium profile, Magnetic door stop



KKP-AR
Linear bearing with inclined ball tracks, Heavy loads / -20°



CAB
Galvanised steel cable, Galvanised steel



LRR-53
Spring loaded latch, Spring return latch - steel

Complementary products



PLC_PLT
Magnetic stud with central hole, With central hole



PLC_PLT
Magnetic stud with threaded hole, With threaded hole