



Magnetic stud with central hole

AlNiCo

VAP



- AlNiCo magnets with central through drilled mounting hole
- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

For recessed mounting, following precautions should be observed

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

*Depending on availability - Dimensions in mm

Our other products



LVT

Miniature motorised actuator 2A, 2 amperers



CHV

Mechanical speed variator, from 0,18 to 1,5kW



VAB

Flanged nut for ball screw, For VAB ballscrew



PML

Solid foot mount for heavy loads, Ø 100, 120 or 150



GTSS

Belt tensioner, For use in hostile environments



CNA-CNG

Right angled mounting plate, Right angled mounting plate for clevis



GP

Spring loaded toggle latch, Standard




HTD8M-BAR

HTD type tooth bar stock, HTD8



DEP

Tools Hygienic Usit® and Hygienic



FF10

Offset spur gear reducer, from 0.78 to



BLM

Spring loaded plunger with ball tip, Plastic



HW_HT

Half-rail guide, Wheel

Complementary products



PLC_PLT

Magnetic stud with central hole, With central hole



PLC_PLT

Magnetic stud with threaded hole, With threaded hole