



Magnetic stud with central hole

AlNiCo

VAP



- AlNiCo magnets with central through drilled mounting hole
- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

For recessed mounting, following precautions should be observed

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

*Depending on availability - Dimensions in mm

Our other products



PGNT
Thermoplastic T handle, With threaded spindle



ADL_M
Male eye bolt conforms to DIN580, Stainless steel



PRF_BP
Doorstop for aluminium profile, Swing door stop




NCT_AT
Variable angle connector, Variable angle



MCLred
Reducing sleeve female/female, Cylindrical - steel



ZG125
Plastic spur gear, Machined plastic (delrin)



LAT1
1A motorised linear actuator, 1 ampere



BPQ
Quadro linear ball bearing unit, Included 4 linear ball bearings



DB
Steel bevel gear, 2:1



DOMI80
Accessories, Clamping lever



WJUM10
Drylin® W bearing block, Slide



BTC
End cap for square tube, Standard

Complementary products



PLC_PLT
Magnetic stud with central hole, With central hole



PLC_PLT
Magnetic stud with threaded hole, With threaded hole