



Magnetic stud with central hole

AlNiCo

VAP



- AlNiCo magnets with central through drilled mounting hole
- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

For recessed mounting, following precautions should be observed

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request


Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

*Depending on availability - Dimensions in mm

Our other products



PPD
Indexing plunger for
sheets, For sheet
metal



PM2
Worm and wheel set,
Bronze



LVT
Miniature motorised
actuator 4A, 4 ampers



CHAsb63
Hinge without pin,
Polymer pin hinge



CHA38_SS
Stainless steel face
frame hinge, Surface
mount



SVT30
Screwjack with
travelling screw, with
translating screw



PCAt herm
Pull handle,
Thermoplastic



AT10-25ECO
AT type timing pulley,
Economy range -
AT10 aluminium



PCS75K
Chain sprocket with
hardened teeth,
19.05mm (DIN12B-1)



HDSS
Needle roller double
universal joint -
Stainless steel, Heavy



PRF4545
Standard aluminium
profile, 45 x 45 mm



PM2
Worm and wheel set,
Machined plastic
(delrin)

Complementary products



PLC_PLT
Magnetic stud with
central hole, With
central hole



PLC_PLT
Magnetic stud with
threaded hole, With
threaded hole