

# Self-gripping cable strip

**VEL** For electric and pneumatic cables

- **Velcro type tie for fixing or bundling cables**

- 1 "loop" side, 1 "hook" side
- Ideal for fixing cables on aluminum profiles with the **VEL-PRF** bases
- Sold in roll
- Materials:  
Self-extinguishing polypropylene according to UL94-V2



## Advantages

- Easy mounting
- Reusable hundreds of times
- Different sizes of hook-and-loop strips available
- No risk of injury or damage to cables unlike Rilsan cable ties
- Cut-out for easy lengthening.

## Accessories

- **VEL-M** or **VEL-PRF** base



Use on the base



Use alone

## DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request

Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

\*Depending on availability - Dimensions in mm

# Clip-on base for hook-and-loop strip

For electric and pneumatic cables

VELPRF

- Support clip for Velcro type hook-and-loop strip

- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:

Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0



## Advantages



- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- VEL stripe



clip-on  
on PRF profile



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	A	B	H1	Price each 1 to 9
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

**VELM** For electric and pneumatic cables

## - Support clip for Velcro type hook-and-loop strip

- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:  
Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0





For 7,5 to 20 mm  
strips

## Advantages

- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- VEL stripe
- PRF-ECL nut and FHC screw



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	A	B	H	Price each 1 to 9
VEL7,5-M4-420	4-20	M4	7,5	18,6	15	8,6	3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

For electric and pneumatic cables

VELM

## - Support clip for Velcro type hook-and-loop strip

- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening

## - Materials:

Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0




For strip  
30mm

## Advantages

- Easy mounting by screwing
- Reusable

## Accessories

- VEL stripe
- PRF-ECL nut and CHC6 screw



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each
VEL30-M6-20100	20-100	M6	30	1 to 9 7,70 €

Dimensions in mm

## Our other products



CHM40-MOT

Asynchronous AC  
motorgearboxes 0.18  
to 0.55kW, 0.18 to  
0.55kW



TAC\_SS

Stainless steel rigging  
screw (hook/eye),  
Stainless steel



SH2

Parallel axis helical  
gear, Machined plastic  
(delrin)



PTGT

Tensioner pulley, For  
V belts



PGR

Folding revolving  
handle for handwheel,  
Folding



DOMI120

Accessories, Plate



KKP-AR

Linear bearing with  
inclined ball tracks,  
Heavy loads / -20°  
+200°



SLV

Vertical toggle clamp,  
Vertical Lever Clamp -  
stainless steel



PCS\_PA6

Plastic sprocket,  
9.525mm (DIN 06B-1)



CHB

Reaction arm, CHB  
gear reducers



CLG3

Moulded plastic spur  
gear, Moulded plastic



GGB

Female wing knob,  
With blind thread

## Complementary products



VEL

Self-gripping cable  
strip, electric and  
pneumatic cables



VELprf

Clip-on base for hook-  
and-loop strip,  
Polyamide



VELM4

Screw-on base for  
hook-and-loop strip,  
Polyamide