

Self-gripping cable strip

VEL For electric and pneumatic cables

- Velcro type tie for fixing or bundling cables
- 1 "loop" side, 1 "hook" side
- Ideal for fixing cables on aluminum profiles with the VEL-PRF bases
- Sold in roll
- Materials:
Self-extinguishing polypropylene according to UL94-V2

Advantages

- Easy mounting
- Reusable hundreds of times
- Different sizes of hook-and-loop strips available
- No risk of injury or damage to cables unlike Rilsan cable ties
- Cut-out for easy lengthening.

Accessories

- VEL-M or VEL-PRF base



Use on the base



Use alone

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request

Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

*Depending on availability - Dimensions in mm

Clip-on base for hook-and-loop strip

For electric and pneumatic cables **VELPRF**

- Support clip for Velcro type hook-and-loop strip
- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
 - Glass fiber reinforced polyamide
 - self-extinguishing according to UL94-V0




Advantages




- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available

Accessories

- VEL stripe



Clip-on
on PRF profile



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. List		-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	For strip			Price each
			A	B	H1	
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	1 to 9 4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

*Depending on availability - Dimensions in mm

Screw-on base for hook-and-loop

VELM For electric and pneumatic cables

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
Glass fiber reinforced polyamide
self-extinguishing according to UL94-V0

Advantages



- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

Accessories

- VEL stripe
- PRF-ECL nut and FHC screw



For 7.5 to 20 mm strips



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	A	B	H	Price each
							1 to 9
VEL7.5-M4-420	4-20	M4	7,5	18,6	15	8,6	3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

*Depending on availability - Dimensions in mm

Screw-on base for hook-and-loop

For electric and pneumatic cables

VELM

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
Glass fiber reinforced polyamide
self-extinguishing according to UL94-V0

Advantages



- Easy mounting by screwing
- Reusable

Accessories

- VEL stripe
- PRF-ECL nut and CHC6 screw



For strip
30mm



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each 1 to 9
VEL30-M6-20100	20-100	M6	30	7,70 €

Dimensions in mm

Our other products



CDR

Retaining cable for ball pin, Retaining cable



PRF_BR

Clamp for aluminium profile, Clamp for profile



EBC

Cap nut Hygienic Design®, Compact



FRtool

Tool for thread repair inserts, Assembly tool



GPBSS

Threaded spherical knob, Stainless steel 304



T5P_T10P

Connecting plate for T type timing belts, T5



T5M_T10M

T type timing belt per metre, T5 Steel cored polyurethane



ARTE

Flexible bush, For multi-directional loads



PDM_PDV

Detectable plastic palm grip, blue thermoplastic



MFBSC

Stainless steel flexible bellows coupling, Stainless steel - with



GG3

Ground spur gear, Heat treated steel



SBF

Sealed flange bearing unit for Food Industry, cover

Complementary products



VEL

Self-gripping cable strip, electric and pneumatic cables



VELprf

Clip-on base for hook-and-loop strip, Polyamide



VELM4

Screw-on base for hook-and-loop strip, Polyamide