

# Self-gripping cable strip

## VEL For electric and pneumatic cables

- Velcro type tie for fixing or bundling cables
- 1 "loop" side, 1 "hook" side
- Ideal for fixing cables on aluminum profiles with the VEL-PRF bases
- Sold in roll
- Materials:  
Self-extinguishing polypropylene according to UL94-V2

### Advantages

- Easy mounting
- Reusable hundreds of times
- Different sizes of hook-and-loop strips available
- No risk of injury or damage to cables unlike Rilsan cable ties
- Cut-out for easy lengthening.

### Accessories

- VEL-M or VEL-PRF base



Use on the base



Use alone

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request

Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

\*Depending on availability - Dimensions in mm

# Clip-on base for hook-and-loop strip

For electric and pneumatic cables **VELPRF**

- Support clip for Velcro type hook-and-loop strip
- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
  - Glass fiber reinforced polyamide
  - self-extinguishing according to UL94-V0




## Advantages




- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- VEL stripe



Clip-on  
on PRF profile



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc. List		-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	For strip			Price each
			A	B	H1	
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	1 to 9 4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

**VELM** For electric and pneumatic cables

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:  
Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0

## Advantages



- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- VEL stripe
- PRF-ECL nut and FHC screw



For 7.5 to 20 mm  
strips



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)		For strips width (mm)			Price each	
	For screw	For screw	A	B	H	1 to 9	
VEL7.5-M4-420	4-20	M4	7,5	18,6	15	8,6	3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

For electric and pneumatic cables

VELM

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:

Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0

## Advantages



- Easy mounting by screwing
- Reusable

## Accessories

- VEL stripe
- PRF-ECL nut and CHC6 screw



For strip  
30mm



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each 1 to 9
VEL30-M6-20100	20-100	M6	30	7,70 €

Dimensions in mm

## Our other products



HG5-ECO

Eco range Spur gear,  
Steel C45



VQTplq

Quarter-turn clamp  
lock - Clamping plate,  
Wall mounting



TSRTC

Stem support for  
caster, For swivel  
caster with central  
hole



PCS25ECO

Chain sprocket - steel,  
6.35mm



GARQT

Quarter turn lock pin  
for clamping, Quarter  
turn



SVT15

Screwjack with  
travelling screw, with  
translating screw




PR882

Idle sprocket for slat  
top chain, Range 882



GLB

Small 6 lobe threaded  
handle - female,  
Technopolymer -  
Stainless steel



MRS

Stainless steel metric  
section rack, Stainless



PCF2

Conical flexible  
mount, Oval base



HAS

Captive C washer,  
Slotted flat headed



CHA35

Hinge for aluminium  
profile, Hinge

## Complementary products



VEL

Self-gripping cable  
strip, electric and  
pneumatic cables



VELprf

Clip-on base for hook-  
and-loop strip,  
Polyamide



VELM4

Screw-on base for  
hook-and-loop strip,  
Polyamide