


- **Operating element**
- **Materials:**  
 Black phenolic Duraplast  
 Threaded stud: stainless steel

### Advantages

- Easy grip
- Temperature resistant
- Good chemical resistance
- Easier to clean than technopolymer
- In machining applications, less likely to retain swarf



Good resistance



### DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØA	ØB	C	ØD	F	G	L	Weight (g)	Price each 1 to 9
VP20-M5-15/SS	20	13	15	M5	7	8	15	9	4,54 €
VP20-M6-15/SS	20	13	15	M6	7	8	15	10	4,68 €
VP20-M6-20/SS	20	13	15	M6	7	8	20	13	4,68 €
VP30-M6-15/SS	30	17	24	M6	11	13	15	20	5,37 €
VP30-M6-20/SS	30	17	24	M6	11	13	20	21	5,55 €
VP30-M6-35/SS	30	17	24	M6	11	13	35	22	5,70 €
VP40-M8-20/SS	40	21	28	M8	12	16	20	42	6,73 €
VP40-M8-30/SS	40	21	28	M8	12	16	30	46	7,35 €
VP40-M8-45/SS	40	21	28	M8	12	16	45	51	8,19 €
VP50-M10-20/SS	50	25	33	M10	13	20	20	73	9,02 €
VP50-M10-30/SS	50	25	33	M10	13	20	30	78	10,02 €
VP50-M10-40/SS	50	25	33	M10	13	20	40	83	10,78 €
VP60-M12-30/SS	60	28	37	M12	15	22	30	118	14,51 €
VP60-M12-40/SS	60	28	37	M12	15	22	40	125	15,58 €

Dimensions in mm

## Our other products




GBSz

Cylindrical ballscrew nut, Cylindrical leadscrew nut



HBM

Adjustment bushing for half-rail guide, Adjustment bushing



IN1

Internal gear, Machined plastic (delrin)



WING

Manually tightened wing nut, Stainless steel DIN 314/315



RBNpl

Swivel castor with double brake, Steel - rubber



DILC

Indexing plunger with cam, with cam



PM2

Worm and wheel set, Non hardened steel



FUSS

Bearing locknut, Self locking locknut - stainless steel lock washer



HLUT

Spoked handwheel with handle,



GARQT

Quarter turn lock pin for clamping, Quarter



HTD5M\_09


HTD Heavy duty timing pulley, HTD5



AC

Strike for toggle latch, 15mm

## Complementary products



VP

Small 6 lobe threaded handle - male, Duroplast - Steel



GLP

Small 6 lobe threaded handle - male, Technopolymer - Stainless steel