



# DryLin® W bearing block






Size 16 - For loads of up to 2100N **WJUM16**

- Material:  
Housing: Zamak  
Liner: iglidur®j200

## Advantages

- Full design flexibility using **WS16** single rails and **WJUM01-16** bearing blocks

**Modular**



## DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Type	backlash	Weight (g)	Max. static load (20°C) Coy (N)	Coz+ (N)	Coz- (N)	Stock*	Price each 1 to 4
WJUM01-16	Fixed	0	100	2100	2100	400	✓	16,64 €
WJUM01-16-LL	Floating	±0,2	100	2100	2100	400	-	16,66 €

\*Depending on availability - Dimensions in mm

## Our other products



V3RA\_PT

3-spoked handwheel  
with handle,  
Polyamide



PCS8ECO

Chain sprocket - steel,  
8mm (DIN 05B-1)



DOG319

Motor-gearbox 12V  
and 24V DC, from 4 to  
9 Nm



PR40

Articulated foot Ø40,  
Ø 40



H0

Crossed helical gear  
crossed axis at 90°,  
Steel 20NCD2



RPCpl

Swivel castor with  
double brake, Steel -  
Polyamide



BLH70

Right angled gearbox,  
from 26 to 128 Nm



PDM\_PDV

Detectable plastic  
palm grip, by metal  
detectors



PPG

Indexing plunger with  
flange, With  
horizontal mounting



BAG

Steel Clamping collar,  
Steel



PW\_PWG2

Worm - precision  
range, Stainless steel



CHMBR

Reaction arm, CHM  
and CHMR gear  
reducers reaction arm

## Complementary products



WS16

Drylin® W rail, Rail



WW16

Drylin® W slide, slide  
assembly



WJRM

Drylin® W hybrid  
bearing block, Hybrid  
bearings