



DryLin®W bearing block






Size 16 - For loads of up to 2100N **WJUM16**

- Material:
Housing: Zamak
Liner: iglidur®j200

Advantages

- Full design flexibility using **WS16** single rails and **WJUM01-16** bearing blocks

Modular



DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Type	backlash	Weight (g)	Max. static load (20°C) Coy (N)	Coz+ (N)	Coz- (N)	Stock*	Price each 1 to 4
WJUM01-16	Fixed	0	100	2100	2100	400	✓	16,64 €
WJUM01-16-LL	Floating	±0,2	100	2100	2100	400	-	16,66 €


*Depending on availability - Dimensions in mm

Our other products



SCA_SS

Stainless steel flat cable clamp, Stainless steel



EZY

Cylindrical stop, Steel



PW_PWG05

Worm - precision range, Stainless steel




METEB

Self-lubricating blanks, Bronze BP25



TRM

Spur round rack, Steel - module 1-6



P15

Worm and wheel gear reducer, up to 3,75 Nm



GBS

Nut for ballscrew, Flanged ballscrew nut




OP3_14_06

Reducing sleeve for OP indicators, Reduction socket



CHA225

Screwed hinge with threaded insert, 225



PTR

Idle chain sprocket, For standard



BOXdh

Boxed set of cylindrical dowel pins



BDP1R

Adjustable support arm, Single clamp

Complementary products



WS16

Drylin® W rail, Rail



WW16

Drylin® W slide, slide assembly



WJRM

Drylin® W hybrid bearing block, Hybrid bearings