







- Material: Hard anodised aluminium
- Standard length : 1000mm
- Other lengths available (up to 4000 mm)
- For bearing **WJUM16** and **WJRM16**, bearing blocks



Modular



DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Length L (mm)	Max. length L (mm)	C5 mini	C5 maxi	ly (mm ⁴)	Iz (mm ⁴)	Wby (mm ³)	Wbz (mm ³)	Weight (kg/m)	Stock*	Price each 1 to 4
WS16	1000	4000	20	79,5	36000	12900	1800	940	0,98	✓	94,51 €
WS16-60	1000	4000	20	79,5	36760	26100	9900	1900	1,96	✓	200,23 €

*Depending on availability - Dimensions in mm

Our other products



PENV

Recessed handle,
screw fixing



CHAR7530

Spring hinge, welded



M0

Worm and wheel set,
Bronze



M

Bellows cover,
Accessory:



MDPOT

Potentiometer,



ACLAPA

Magnetic stop for
aluminium profile,
Magnetic stop



MLY_SS

Stainless steel bow
shackle with eye bolt,
Stainless steel



PTA80

Articulated levelling
foot, pressed base
Ø80, Ø 80



IBJ

180° ball and socket
joints, Steel



BMM

Knurled knob - male,
Knurled



AT5M AT10M

AT type timing belt
per metre, AT10 Steel



M1

Worm and wheel set,
Non hardened steel

Complementary products



WJUM16

Drylin® W bearing
block, Slide



WW16

Drylin® W slide, slide
assembly



WJRM

Drylin® W hybrid
bearing block, Hybrid
bearings