






- Material: Hard anodised aluminium
- Standard length : 1000mm
- Other lengths available (up to 4000 mm)
- For bearing **WJUM16** and **WJRM16**, bearing blocks



Modular



DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Length L (mm)	Max. length L (mm)	C5 mini	C5 maxi	ly (mm ⁴)	Iz (mm ⁴)	Wby (mm ³)	Wbz (mm ³)	Weight (kg/m)	Stock*	Price each 1 to 4
WS16	1000	4000	20	79,5	36000	12900	1800	940	0,98	✓	94,51 €
WS16-60	1000	4000	20	79,5	36760	26100	9900	1900	1,96	✓	200,23 €

*Depending on availability - Dimensions in mm

Our other products



CLB_M

Die cast zinc clamping lever - female, Zamak



J51

Spur gear coaxial gearbox, from 0.13 to 0.49 Nm - Inline



HTD5M_09

HTD Heavy duty timing pulley, HTD5 Steel



NCT

Square tube connector, Fixed angle



VCMB

Dual-thread screw wood/metal, Stainless steel



SSDB

Stainless steel bevel gear, 2:1



CLASS

Stainless steel indexing handle - male, Stainless steel



FTSN

Supported shaft for linear guide, Steel shaft / Aluminium support



VRM

Female swivelling lifting rings, Female



HDSS

Needle roller double universal joint -



GMK17_BROSSE

Brush strip, Cone-shaped - brush



BAN

Angular clamp, Universal

Complementary products



WJUM16

Drylin® W bearing block, Slide



WW16

Drylin® W slide, slide assembly



WJRM

Drylin® W hybrid bearing block, Hybrid bearings