






- Material: Hard anodised aluminium
- Standard length : 1000mm
- Other lengths available (up to 4000 mm)
- For bearing **WJUM16** and **WJRM16**, bearing blocks



**Modular**




### DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-10%	-15%	-20%	On request

Part number	Length L (mm)	Max. length L (mm)	C5 mini	C5 maxi	ly (mm <sup>4</sup> )	lz (mm <sup>4</sup> )	Wby (mm <sup>3</sup> )	Wbz (mm <sup>3</sup> )	Weight (kg/m)	Stock*	Price each 1 to 4
WS16	1000	4000	20	79,5	36000	12900	1800	940	0,98	✓	94,51 €
WS16-60	1000	4000	20	79,5	36760	26100	9900	1900	1,96	✓	200,23 €

\*Depending on availability - Dimensions in mm

## Our other products



GLT2-27

Telescopic drawer runners for groove mounting, Partial extension



NRV

Orthogonal support clamp, Orthogonal support clamp



CHTRP

Single and dual output gearboxes, Up to 75,7 Nm



PTA150

Articulated levelling foot, pressed base Ø150, Ø150



M2

Worm and wheel set, Bronze



ZHG6

Plastic spur gear, Machined plastic (delrin)




UGAC\_UGET

Actuator guide kit, Coupling for threaded cylinder end




PSG1

Spur gear - precision range, Case hardened steel 20NCD2



PRF\_TOOL

Assembly key for aluminium profile,



SLS

Bearing block for leadscrew, Fixed



NKXR

Combined bearing without inner ring,



PR881

Idler sprocket for slat top chain, Range 881

## Complementary products



WJUM16

Drylin® W bearing block, Slide



WW16

Drylin® W slide, slide assembly



WJRM

Drylin® W hybrid bearing block, Hybrid bearings