



- Hardened and ground shaft for linear guidance with threaded holes

- Material:

Hardened ground steel Ck55



Tapped holes



DISCOUNTS

Qty	1+	2+	4+	8+
Disc.	List	-15%	-20%	On request

Part number	ØD (h6)	Length L (mm)	F	ØM	P	Weight (kg)	Stock*	Price each
Z12-100A-M5/M5	12	100	1,8	M5	10	0,089	-	33,09 €
Z12-200A-M5/M5	12	200	1,8	M5	10	0,178	-	38,28 €
Z12-300A-M5/M5	12	300	1,8	M5	10	0,267	-	43,47 €
Z12-400A-M5/M5	12	400	1,8	M5	10	0,356	-	48,63 €
Z12-500A-M5/M5	12	500	1,8	M5	10	0,445	-	53,82 €
Z12-600A-M5/M5	12	600	1,8	M5	10	0,534	-	58,98 €
Z16-100A-M6/M6	16	100	2,0	M6	12	0,157	-	39,48 €
Z16-200A-M6/M6	16	200	2,0	M6	12	0,314	-	45,96 €
Z16-300A-M6/M6	16	300	2,0	M6	12	0,471	-	52,44 €
Z16-400A-M6/M6	16	400	2,0	M6	12	0,628	-	58,92 €
Z16-500A-M6/M6	16	500	2,0	M6	12	0,785	-	65,43 €
Z16-600A-M6/M6	16	600	2,0	M6	12	0,942	-	71,91 €
Z16-700A-M6/M6	16	700	2,0	M6	12	1,099	-	78,39 €
Z16-800A-M6/M6	16	800	2,0	M6	12	1,256	-	84,87 €
Z20-100A-M8/M8	20	100	2,2	M8	16	0,245	-	41,64 €
Z20-200A-M8/M8	20	200	2,2	M8	16	0,490	-	49,08 €
Z20-300A-M8/M8	20	300	2,2	M8	16	0,735	-	56,49 €
Z20-400A-M8/M8	20	400	2,2	M8	16	0,980	-	63,93 €
Z20-500A-M8/M8	20	500	2,2	M8	16	1,225	-	71,34 €
Z20-600A-M8/M8	20	600	2,2	M8	16	1,470	-	78,75 €
Z20-700A-M8/M8	20	700	2,2	M8	16	1,715	-	86,19 €
Z20-800A-M8/M8	20	800	2,2	M8	16	1,960	-	93,60 €
Z20-900A-M8/M8	20	900	2,2	M8	16	2,205	-	101,04 €
Z20-1000A-M8/M8	20	1000	2,2	M8	16	2,450	-	108,48 €
Z25-100A-M10/M10	25	100	2,5	M10	20	0,383	-	51,42 €
Z25-200A-M10/M10	25	200	2,5	M10	20	0,766	-	60,27 €
Z25-300A-M10/M10	25	300	2,5	M10	20	1,149	-	69,15 €
Z25-400A-M10/M10	25	400	2,5	M10	20	1,532	-	78,03 €
Z25-500A-M10/M10	25	500	2,5	M10	20	1,915	-	86,91 €
Z25-600A-M10/M10	25	600	2,5	M10	20	2,298	-	95,76 €
Z25-700A-M10/M10	25	700	2,5	M10	20	2,681	-	104,64 €
Z25-800A-M10/M10	25	800	2,5	M10	20	3,064	-	113,49 €
Z25-900A-M10/M10	25	900	2,5	M10	20	3,447	-	122,37 €
Z25-1000A-M10/M10	25	1000	2,5	M10	20	3,830	-	131,25 €

*Dans la limite du disponible - Dimensions en mm

Our other products



PTA100ssEB
Articulated foot with sheet metal base Ø100, Articulated foot



DCG
Suction cup, 2.5 bellows, nitrile



WJUM10
Drylin® W bearing block, Slide



PM2
Worm and wheel set, Bronze



EKN
Bellows coupling Gerwah®, from 0.5 to 12Nm



BOX-TOR-B
Box set of Nitrile O-rings in nitrile, 20.38 x 1.78mm to 50.16 x 5.34



KSTM
Igubal® pillow block bearing, Polymer



ZHBRA
Plastic bevel gear, 1,25:1 2:1 3:1




BOX-TOR-TOOL
Box set of tool for Nitrile O-rings, Extraction tools



DER71
Stainless steel AC asynchronous motor 0.25 à 0.37kW, 0.25



PM3
Worm and wheel set, Non hardened steel



LRH
Bi-directional leadscrew, Bi-directional - 1 thread

Complementary products




ZA
Shaft for linear guides, Hardened ground steel



BPQ
Quadro linear ball bearing unit, Included 4 linear ball bearings



ZB
Shaft for linear guides, Hardened ground stainless steel



FTSN
Supported shaft for linear guide, Steel shaft / Aluminium support