

# Rotating bent lever

New

GT64  
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


## Info

- The approximate fitting size:  $X = 32,7 \text{ mm}$  for a tension of about 60 daN.
- Usable hook: **AC161**

NEW!



Application example



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
<b>Bent lever</b>							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
<b>Hook</b>							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

HPC

WEB  
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Increased fitting tolerances

## GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:


White galvanised steel or stainless steel

### Advantage


- Compensation for tolerances on fitting sizes by 4 springs.

### Info

- The approximate fitting size:  $X = 31,4 \text{ mm}$  for a tension of about 60 daN.
- Usable hook: **AC161**



GT64R



AC161

### DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
<b>Bent lever</b>							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
<b>Hook</b>							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm


## Our other products



PTMR  
Telescopic furniture  
foot, threaded stud



RT70  
Self-centering locking  
Assembly,  
Medium/high torque



PRZ  
Wear strip for slat top  
chain, Z profile to be  
filled



VTH  
Hexagonal headed  
bolts, Steel class 8.8



CLSCLP\_SS  
Clevis components,  
short version,  
Stainless steel - short  
range



PPS  
Lifting ring, Universal  
threaded



HTD5M\_15  
HTD Heavy duty  
timing pulley, HTD5  
Aluminium



S\_2RS  
Deep groove ball  
bearing, Stainless  
steel



PCS50SS  
Chain sprocket -  
Stainless steel,  
12.7mm (DIN 08B-1)



CHM50  
Worm and wheel gear  
reducer, up to 107  
Nm



ACLERP  
Roller block for  
aluminium profile,  
Without guide rail



AZY\_SS  
Stainless steel  
cylindrical elastomount, Stainless steel

## Complementary products



gt64r  
Rotating bent lever  
with spring, Increased  
fitting tolerances