

Rotating bent lever

New

GT64
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


Info

- The approximate fitting size: X = 32,7 mm for a tension of about 60 daN.
- Usable hook: AC161

NEW!



Application example



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

New

Rotating bent lever with spring

Increased fitting tolerances

GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:



White galvanised steel or stainless steel

Advantage

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4 \text{ mm}$ for a tension of about 60 daN.
- Usable hook: **AC161**

**GT64R****AC161**

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm

Our other products



LF

Precision locknut,
Precision locknut



WJUM16

Drylin® W bearing
block, Slide



BOXKU

Boxed set of half
round (Woodruff) keys
NFE22179, Boxed set
of half ...



MRA_SS

Stainless steel Quick
link, Stainless steel



CHAE4080PA

Symmetrical decorative
screwed hinge,
Polyamide



CNA-CNG

Right angled
mounting plate, Right
angled mounting
plate for ball jo...



BABTV

Ball lock pins lockable
, Stainless steel



UCFL_SS

Stainless steel flanged
bearing, Stainless
steel



GPLny

Brush, nylon



ESCON

Speed controller 5A, 5
A



BOX-TOR-H

Box set of Nitrile O-
rings in nitrile, 3.00 x



HG8-ECO

Eco range Spur gear,
Steel C45

Complementary products



gt64

Rotating bent lever,
Common applications