

Rotating bent lever

New

GT64
AC161

Common applications



- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an **AC161 hook** is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:

White galvanised steel or stainless steel


Info

- The approximate fitting size: X = 32,7 mm for a tension of about 60 daN.
- Usable hook: **AC161**

NEW!



Application example



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. Price		-3%	-5%	On request

Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. Stroke	Max. tension (daN)	Weight (g)	Price each 1 to 9
Bent lever							
GT64-ZB	White galvanised steel	15/10è	12/10è	6	80	39	8,12 €
GT64-SS	Rough 303 stainless steel	15/10è	12/10è	6	80	39	10,12 €
Hook							
AC161-ZB	White galvanised steel	15/10è	12/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	12/10è	-	-	3,7	0,39 €

Dimensions in mm

New

Rotating bent lever with spring

Increased fitting tolerances

GT64R AC161

- Closure by eccentric cam by turning the butterfly nut
- Automatic return of the butterfly nut by a spring system.
- Model designed to be hung in a recess (use of an AC161 hook is possible but not essential)
- Good tensile strength.
- Easy to operate
- Smaller footprint
- In the open position, the unit folds down completely.
- Lead sealing option
- Very high safety against accidental opening (e.g. during vibration).
- Allows for seamless use and greater flexibility in positioning tolerances.
- Material:



White galvanised steel or stainless steel

Advantage

- Compensation for tolerances on fitting sizes by 4 springs.

Info

- The approximate fitting size: $X = 31,4$ mm for a tension of about 60 daN.
- Usable hook: **AC161**

**GT64R****AC161**

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	Price	-3%	-5%	On request


Part number	Material	Thickness latching tab	Thickness retaining bracket	Max. tension (daN)	Stroke	Weight (g)	Price each 1 to 9
Bent lever							
GT64R-ZB	White galvanised steel	15/10è	20/10è	6	80	39	10,93 €
GT64R-SS	Rough 303 stainless steel	15/10è	20/10è	6	80	39	13,27 €
Hook							
AC161-ZB	White galvanised steel	15/10è	20/10è	-	-	3,7	0,29 €
AC161-SS	Rough 303 stainless steel	15/10è	20/10è	-	-	3,7	0,39 €

Dimensions in mm

Our other products



TB8
Cylindrical roller thrust bearing, Steel



GMK17_P
Flat Guide, Flat guide for conical profile



BPMc
Stainless steel slotted spring plunger with ceramic ball tip, 303 St...



CLAT
Clamping lever Hygienic Usit® - male, Stainless steel



CQA30
Accessory for adjustment slide-system, 30



SVT5
Screwjack with travelling screw, with translating screw



GSI_A
Gas control screw for gas spring, Gas control screw



CABtool
Fitting cable tools, Cutting tools



CLG1
Moulded plastic spur gear, Moulded plastic



DOMI120
Domino 120 adjustable slide, Slide



ZG1
Plastic spur gear, Machined plastic



BFA
Shaft locking washer, E clip

Complementary products



gt64
Rotating bent lever, Common applications