



## Torque up to 22Nm

# CHM30-MOT

- Three phase electric motor gearbox assembly
- Comprises 1 CHM30 gearbox and 1 CHT motor (see motor section)
- 4 pole motor
- B14 mounting flange
- Motor speed 1,400 rpm
- Material:  
Gearbox housing: aluminium




### Wiring

- Wiring diagrams N°3 and N°5 on technical information pages (tome 2 p.314)

### Accessories

- Output shaft  
CHM30-X,  
CHM30-DX  
(tome 2 p.313)
- Reaction arm  
CHM30-BR  
(tome 2 p.312)



### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ratio	Motor	Motor power (kW)	Speed under load (rpm)	Nominal Torque (Nm)	Service factor	Stock*	Price each
CHM30-7-63C4	7.5:1	63C4	0,22	186,7	9	2,1	✓	255,00 €
CHM30-10-63C4	10:1	63C4	0,22	140,0	11	1,6	✓	255,00 €
CHM30-15-63C4	15:1	63C4	0,22	93,3	16	1,0	✓	254,45 €
CHM30-20-63C4	20:1	63C4	0,22	70,0	20	0,9	✓	254,45 €
CHM30-25-63B4	25:1	63B4	0,18	56,0	20	1,0	✓	249,04 €
CHM30-30-63B4	30:1	63B4	0,18	46,7	22	0,9	✓	249,04 €
CHM30-40-63B4	40:1	63B4	0,18	35,0	21	0,8	✓	249,04 €
CHM30-50-63B4	50:1	63B4	0,18	28,0	19	0,8	✓	249,04 €
CHM30-60-56B4	60:1	56B4	0,09	23,3	18	0,9	✓	239,72 €
CHM30-80-56B4	80:1	56B4	0,09	17,5	13	0,9	✓	239,72 €

\*Depending on availability - Dimensions in mm



## CHM40 -MOT

### Torque up to 52Nm

- Three phase electric motor gearbox assembly
- Comprises 1 CHM40 gearbox and 1 CHT motor (see motor section)
- 4 pole motor
- B14 mounting flange
- Motor speed 1,400 rpm
- Material:  
Gearbox housing: aluminium




### Wiring

- Wiring diagrams N°3 and N°5 on technical (tome 2 p.314)

### Accessories

- Output shaft  
CHM40-X,  
CHM40-DX  
(tome 2 p.313)
- Reaction arm  
CHM40-BR  
(tome 2 p.312)



### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ratio	Motor	Motor power (kW)	Speed under load (rpm)	Nominal Torque (Nm)	Service factor	Stock*	Price each
CHM40-7-71C4	7,5:1	71C4	0,55	186,7	22	1,6	✓	319,39 €
CHM40-10-71C4	10:1	71C4	0,55	140,0	30	1,4	✓	319,39 €
CHM40-15-71C4	15:1	71C4	0,55	93,3	44	0,9	✓	319,39 €
CHM40-20-71C4	20:1	71C4	0,55	70,0	38	1,0	-	319,39 €
CHM40-25-71B4	25:1	71B4	0,37	56,0	45	0,9	✓	300,26 €
CHM40-30-71B4	30:1	71B4	0,37	46,7	52	0,8	✓	300,26 €
CHM40-40-71A4	40:1	71A4	0,25	35,0	43	0,9	✓	285,70 €
CHM40-50-63C4	50:1	63C4	0,22	28,0	44	0,9	✓	282,01 €
CHM40-60-63B4	60:1	63B4	0,18	23,3	42	0,8	-	276,07 €
CHM40-80-63B4	80:1	63B4	0,18	17,5	36	0,8	✓	276,07 €
CHM40-100-63B4	100:1	63B4	0,18	14,0	35	0,8	✓	276,07 €

\*Depending on availability - Dimensions in mm



- Three phase electric motor gearbox assembly
- Comprises 1 CHM50 gearbox and 1 CHT motor (see motor section)
- 4 pole motor
- B14 mounting flange
- Motor speed: 1,400 rpm
- Material:  
Gearbox housing: aluminium




### Wiring

- Wiring diagrams N°3 and N°5 on technical information pages (tome 2 p.314)

### Accessories

- Output shaft  
**CHM50-X,**  
**CHM50-DX**  
(tome 2 p.313)
- Reaction arm  
**CHM50-BR**  
(tome 2 p.312)



### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

\* without CHM50-100-63B4 mounting flange B5

Part number	Ratio	Motor	Motor power (kW)	Speed under load (rpm)	Nominal Torque (Nm)	Service factor	Price each
CHM50-7-80B4	7,5:1	80B4	0,75	186,7	33,3	2,0	389,74 €
CHM50-10-80B4	10:1	80B4	0,75	140,0	43,9	1,6	389,74 €
CHM50-15-80B4	15:1	80B4	0,75	93,3	62,6	1,2	389,74 €
CHM50-20-80B4	20:1	80B4	0,75	70,0	80,0	0,9	389,74 €
CHM50-25-80A4	25:1	80A4	0,55	56,0	70,0	1,0	372,70 €
CHM50-30-80A4	30:1	80A4	0,55	46,7	80,0	1,0	372,70 €
CHM50-40-71B4	40:1	71B4	0,37	35,0	67,0	1,1	345,86 €
CHM50-50-71B4	50:1	71B4	0,37	28,0	78,0	0,9	345,86 €
CHM50-60-71B4	60:1	71B4	0,37	23,3	87,0	0,8	345,86 €
CHM50-80-71A4	80:1	71A4	0,25	17,5	70,0	0,9	331,28 €
CHM50-100-63B4*	100:1	63B4	0,18	14,0	59,0	0,9	321,66 €

Dimensions in mm

## CHM63-MOT

Torque up to 165Nm

- Three phase electric motor gearbox assembly
- Comprises 1 CHM63 gearbox and 1 CHT motor (see motor section)
- 4 pole motor
- B14 mounting flange
- Motor speed 1,400 rpm
- Material:  
Gearbox housing: aluminium




### Wiring

- Wiring diagrams N°3 and N°5 on technical information pages (tome 2 p.314)

### Accessories

- Servo amplifier  
TEL-ATV11/370
- Output shaft  
CHM63-X,  
CHM63-DX  
(tome 2 p.313)
- Reaction arm  
CHM63-BR  
(tome 2  
p.312- p.314)



### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ratio	Motor	Motor power (kW)	Speed under load (rpm)	Nominal Torque (Nm)	Service factor	Price each
CHM63-7-90L4	7,5:1	90L4	1,50	186,7	67,4	1,8	538,97 €
CHM63-10-90L4	10:1	90L4	1,50	140,0	88,6	1,4	538,97 €
CHM63-15-90L4	15:1	90L4	1,50	93,3	126,0	1,1	538,97 €
CHM63-20-90L4	20:1	90L4	1,50	70,0	164,0	0,8	538,97 €
CHM63-25-90S4	25:1	90S4	1,10	56,0	145,0	0,9	509,35 €
CHM63-30-90S4	30:1	90S4	1,10	46,7	165,0	1,0	509,35 €
CHM63-40-80B4	40:1	80B4	0,75	35,0	143,0	1,0	474,43 €
CHM63-50-80A4	50:1	80A4	0,55	28,0	122,0	1,1	457,42 €
CHM63-60-80A4	60:1	80A4	0,55	23,3	138,0	0,9	457,42 €
CHM63-80-71B4	80:1	71B4	0,37	17,5	114,0	1,1	430,60 €
CHM63-100-71B4	100:1	71B4	0,37	14,0	127,0	0,9	430,60 €

Dimensions in mm


# Comparison of the two technologies (AC)

## Synchronous and Asynchronous

The range of AC motors uses permanent magnet **synchronous** and **asynchronous** single-phase or three-phase technologies.

AC motors are often used in fixed-speed, fixed-torque drives powered directly from the network tension. They offer the long life required for most applications.

<b>Synchronous motors</b>	<b>Asynchronous motors</b>
<p><b>Synchronous motors</b> enable rotate at a fixed and precise speed, independent of load and voltage variations.</p>	<p><b>Asynchronous motors</b> are characterised by a rotation speed that depends on the load applied to the shaft. The speed is linked to the frequency of the singlephase or three-phase supply network (230/400V-50Hz).</p>
<p><b>General characteristics</b></p> <ul style="list-style-type: none"> <li>- The rotor consists of a magnet or electromagnet.</li> <li>- The motor rotates at the same speed as the magnetic field. The rotor is said to rotate at synchronous speed.</li> </ul>	<p><b>General characteristics</b></p> <ul style="list-style-type: none"> <li>- The rotor is made up of rings that form a squirrel cage.</li> <li>- The shaft speed and the magnetic field are out of phase. The rotor rotates more slowly and never reaches synchronous speed.</li> </ul>
<p><b>Benefits</b></p> <ul style="list-style-type: none"> <li>- Better efficiency than asynchronous motors.</li> <li>- Fixed speed, whatever the load.</li> </ul>	<p><b>Benefits</b></p> <ul style="list-style-type: none"> <li>- Highly resistant.</li> <li>- Easy to maintain.</li> <li>- Cheaper and smaller than synchronous motors.</li> <li>- These are the motors most commonly used in industry.</li> </ul>
<p><b>Disadvantage</b></p> <ul style="list-style-type: none"> <li>- Stalls when maximum torque is exceeded</li> </ul>	<p><b>Disadvantage</b></p> <ul style="list-style-type: none"> <li>- Lower efficiency than synchronous motors.</li> </ul>
<p><b>Service life</b></p> <ul style="list-style-type: none"> <li>- It depends on the application and is limited by the life of the motor bearings</li> </ul>	



# Worm and wheel gearbox



## CHMR30


Torque up to 28 Nm

- Ratios from 7.5:1 to 80:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR30
- Materials:
  - Casing: aluminium
  - Screws: hardened steel
  - Wheel: bronze (cast iron hub)
- Lubrication: synthetic oil ISO VG320
- Weight: 1.2 kg



### Accessories

- Output shaft CHM30-X or CHM30-DX (tome 2 p.313)
- Torque arm CHM30-BR (tome 2 p.312)



### Output torque (Nm values given as a guide only)

Ratios	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	
INPUT SPEED (rpm)	2800	12	12	12	11	15	14	13	12	11	10
900	17	17	17	17	20	20	19	17	16	15	12
500	19	19	19	19	22	22	20	19	17	16	14

### DISCOUNTS

Qty	1+	3+	6+
Disc.	List -20%	On request	On request

Part number	Ratio	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock*	Price each 1 to 2
CHMR30-7	7,5:1	2800	373,33	NC	no	✓	143,28 €
CHMR30-10	10:1	2800	280,00	NC	no	✓	143,28 €
CHMR30-15	15:1	2800	186,66	NC	no	✓	143,28 €
CHMR30-20	20:1	2800	140,00	NC	no	-	143,28 €
CHMR30-25	25:1	2800	112,00	NC	no	✓	143,28 €
CHMR30-30	30:1	2800	93,33	NC	not defined	-	143,28 €
CHMR30-40	40:1	2800	70,00	NC	not defined	✓	143,28 €
CHMR30-50	50:1	2800	56,00	NC	not defined	✓	143,28 €
CHMR30-60	60:1	2800	46,66	NC	yes	✓	143,28 €
CHMR30-80	80:1	2800	35,00	NC	yes	✓	143,28 €

\*Depending on availability - Dimensions in mm



# Worm and wheel gearbox


**Torque up to 28 Nm**

**CHM30**

- Ratios from 7,5:1 to 80:1
- With mounting flange B14 for IEC56
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Material:
  - Casing: aluminium
  - Worm: hardened steel
  - Wheel: bronze (cast iron hub)
- Lubrication: synthetic oil ISO VG320
- Weight: 1,2 kg

## Accessories

- Output shaft CHM30-X or CHM30-DX (tome 2 p.313)
- Torque arm CHM30-BR (tome 2 p.312)



## Output torque (Nm values given as a guide only)

Ratios	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1
INPUT	2800	12	12	12	11	15	14	13	12	11
SPEED	1400	17	17	17	17	20	20	19	16	15
(rpm)	900	19	19	19	19	22	20	19	17	16
	500	23	23	23	22	28	25	22	20	18

## DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Input flange	ØD	ØC	ØP	ØE	Static self-locking output	Stock*	Price each 1 to 2
CHM30-7	7,5:1	56B14	9	50	65	80	no	-	143,28 €
CHM30-10	10:1	56B14	9	50	65	80	no	✓	143,28 €
CHM30-15	15:1	56B14	9	50	65	80	no	✓	143,28 €
CHM30-20	20:1	56B14	9	50	65	80	no	✓	143,28 €
CHM30-25	25:1	56B14	9	50	65	80	no	✓	143,28 €
CHM30-30	30:1	56B14	9	50	65	80	not defined	-	143,28 €
CHM30-40	40:1	56B14	9	50	65	80	not defined	-	143,28 €
CHM30-50	50:1	56B14	9	50	65	80	not defined	✓	143,28 €
CHM30-60	60:1	56B14	9	50	65	80	yes	✓	143,28 €
CHM30-80	80:1	56B14	9	50	65	80	yes	✓	143,28 €

\*Depending on availability - Dimensions in mm

# Worm and wheel gearbox



## CHMR40

## Torque up to 57 Nm

- Ratios from 7.5:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Materials:

Casing: aluminium

Screws: treated steel 20CR


Wheel: bronze CuSn12 (cast iron hub G500)

- Lubrication: synthetic oil ISO VG320

- Weight: 2.3 kg

### Accessories

- Output shaft **CHM40-X** or **CHM40-DX** (tome 2 p.313)
- Torque arm **CHM40-BR** (tome 2 p.312)



### Output torque (Nm values given as a guide only)

Ratios	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1	
INPUT SPEED (rpm)	2800	27	26	30	28	27	33	30	30	27	24	22
900 (rpm)	1400	39	39	39	38	39	44	40	38	35	32	28
500 (rpm)	500	52	52	54	53	51	57	52	48	45	40	35

### DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock*	Price each 1 to 2
CHMR40-7	7.5:1	800	373,33	NC	no	✓	172,96 €
CHMR40-10	10:1	2800	280,00	NC	no	✓	172,96 €
CHMR40-15	15:1	2800	186,66	NC	no	-	172,96 €
CHMR40-20	20:1	2800	140,00	NC	no	✓	172,96 €
CHMR40-25	25:1	2800	112,00	NC	no	-	172,96 €
CHMR40-30	30:1	2800	93,33	NC	no	✓	172,96 €
CHMR40-40	40:1	2800	70,00	NC	no	✓	172,96 €
CHMR40-50	50:1	2800	56,00	NC	not defined	-	172,96 €
CHMR40-60	60:1	2800	46,66	NC	not defined	✓	172,96 €
CHMR40-80	80:1	2800	35,00	NC	yes	✓	172,96 €
CHMR40-100	100:1	2800	28,00	NC	yes	✓	172,96 €

\*Depending on availability - Dimensions in mm



# Worm and wheel gearbox

**Torque up to 57 Nm**


**CHM40**

- Ratios from 7.5:1 to 100:1
- With B14 (IEC56) flange
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR40
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G500)
- Lubrication: synthetic oil ISO VG320
- Weight: 2.3 kg



## Accessories

- Output shaft **CHM40-X** or **CHM40-DX** (tome 2 p.313)
- Torque arm **CHM40-BR** (tome 2 p.312)



Output torque (Nm values given as a guide only)

Ratios	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT SPEED (rpm)	2800	27	26	30	28	27	33	30	30	27	24
	1400	39	39	39	38	39	44	40	38	35	28
	900	43	43	44	43	43	48	44	41	38	31
	500	52	52	54	53	51	57	52	48	45	35

## DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Input flange	ØD	ØC	ØP	ØE	Static self-locking output	Stock*	Price each 1 to 2
CHM40-7	7.5:1	63B14	11	60	75	90	no	✓	172,96 €
CHM40-10	10:1	63B14	11	60	75	90	no	✓	172,96 €
CHM40-15	15:1	63B14	11	60	75	90	no	-	172,96 €
CHM40-20	20:1	63B14	11	60	75	90	no	✓	172,96 €
CHM40-25	25:1	63B14	11	60	75	90	no	-	172,96 €
CHM40-30	30:1	63B14	11	60	75	90	no	✓	172,96 €
CHM40-40	40:1	63B14	11	60	75	90	no	✓	172,96 €
CHM40-50	50:1	63B14	11	60	75	90	not defined	✓	172,96 €
CHM40-60	60:1	63B14	11	60	75	90	not defined	✓	172,96 €
CHM40-80	80:1	63B14	11	60	75	90	yes	✓	172,96 €
CHM40-100	100:1	63B14	11	60	75	90	yes	✓	172,96 €

\*Depending on availability - Dimensions in mm

# Worm and wheel gearbox



## CHMR50


## Torque up to 107 Nm

- Ratios from 7.5:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G500)
- Lubrication: synthetic oil ISO VG320
- Weight: 3.5 kg



### Accessories

- Output shaft CHM50-X or CHM50-DX (tome 2 p.313)
- Torque arm CHM50-BR (tome 2 p.312)



### Output torque (Nm values given as a guide only)

Ratios	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1	
INPUT SPEED (rpm)	2800	51	53	56	52	51	63	58	52	49	44	39
500	102	102	102	92	90	107	97	90	82	74	64	54

### DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock*	Price each 1 to 2
CHMR50-7	7,5:1	2800	373,33	NC	no	✓	223,01 €
CHMR50-10	10:1	2800	280,00	NC	no	✓	223,01 €
CHMR50-15	15:1	2800	186,66	NC	no	✓	223,01 €
CHMR50-20	20:1	2800	140,00	NC	no	✓	223,01 €
CHMR50-25	25:1	2800	112,00	NC	no	-	223,01 €
CHMR50-30	30:1	2800	93,33	NC	no	✓	223,01 €
CHMR50-40	40:1	2800	70,00	NC	no	✓	223,01 €
CHMR50-50	50:1	2800	56,00	NC	not defined	✓	223,01 €
CHMR50-60	60:1	2800	46,66	NC	not defined	✓	223,01 €
CHMR50-80	80:1	2800	35,00	NC	yes	✓	223,01 €
CHMR50-100	100:1	2800	28,00	NC	yes	✓	223,01 €

\*Depending on availability - Dimensions in mm



# Worm and wheel gearbox



## CHMR63

## Torque up to 196 Nm

- Ratios from 7.5:1 to 100:1

- Output backlash: N/A

- Max. input speed: 2,800 rpm

- Materials:

Casing: aluminium

Screws: treated steel 20CR

Wheel: bronze CuSn12 (cast iron hub G500)

- Lubrication: synthetic oil ISO VG320

- Weight: 6.2 kg


### Accessories

- Output shaft CHM63-X or CHM63-DX

(tome 2 p.313)

- Torque arm CHM63-BR

(tome 2 p.312)



Output torque (Nm values given as a guide only)

Ratios	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	92	96	102	99	91	119	107	99	94	73
SPEED (rpm)	1400	127	129	139	134	129	159	144	134	129	117
	900	150	152	154	147	136	174	159	144	137	127
	500	183	184	186	177	163	198	184	172	159	136

### DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock*	Price each 1 to 2
CHMR63-7	7,5:1	2800	373,33	NC	no	✓	315,95 €
CHMR63-10	10:1	2800	280,00	NC	no	✓	315,95 €
CHMR63-15	15:1	2800	186,66	NC	no	-	315,95 €
CHMR63-20	20:1	2800	140,00	NC	no	✓	315,95 €
CHMR63-25	25:1	2800	112,00	NC	no	✓	315,95 €
CHMR63-30	30:1	2800	93,33	NC	no	✓	315,95 €
CHMR63-40	40:1	2800	70,00	NC	no	✓	315,95 €
CHMR63-50	50:1	2800	56,00	NC	not defined	-	315,95 €
CHMR63-60	60:1	2800	46,66	NC	not defined	✓	315,95 €
CHMR63-80	80:1	2800	35,00	NC	yes	✓	315,95 €
CHMR63-100	100:1	2800	28,00	NC	yes	✓	315,95 €

\*Depending on availability - Dimensions in mm




# Worm and wheel gearbox

Torque up to 196 Nm


CHM63

- Ratios from 7.5:1 to 100:1
- With B14 flange acc IEC80 for ratios 7.5:1 to 30:1
- With B14 mounting flange acc IEC71 for ratios 7.5:1 to 30:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR63
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G500)
- Lubrication: synthetic oil ISO VG320
- Weight: 3.5 kg



## Accessories

- Output shaft CHM63-X or CHM63-DX (tome 2 p.313)
- Torque arm CHM63-BR (tome 2 p.312)



## Output torque (Nm values given as a guide only)

Ratios	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT SPEED (rpm)	2800	92	96	102	99	91	119	107	99	94	73
2800	127	129	139	134	129	159	144	134	129	121	117
1500	150	152	154	147	136	174	159	144	137	127	123
500	183	184	186	177	163	198	184	172	159	136	127

## DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-20%	On request

Part number	Ratio	Input flange	ØD	ØC	ØP	ØE	Static self-locking output	Stock*	Price each 1 to 2
CHM63-7	7.5:1	80B14	19	80	100	120	no	-	315,95 €
CHM63-10	10:1	80B14	19	80	100	120	no	-	315,95 €
CHM63-15	15:1	80B14	19	80	100	120	no	✓	315,95 €
CHM63-20	20:1	80B14	19	80	100	120	no	-	315,95 €
CHM63-25	25:1	80B14	19	80	100	120	no	-	315,95 €
CHM63-30	30:1	80B14	19	80	100	120	no	✓	315,95 €
CHM63-40	40:1	71B14	14	70	85	105	no	✓	315,95 €
CHM63-50	50:1	71B14	14	70	85	105	not defined	✓	315,95 €
CHM63-60	60:1	71B14	14	70	85	105	not defined	✓	315,95 €
CHM63-80	80:1	71B14	14	70	85	105	oui	✓	315,95 €
CHM63-100	100:1	71B14	14	70	85	105	oui	✓	315,95 €

\* Depending on availability - Dimensions in mm

# Worm and wheel gearbox



## CHMR75

## Torque up to 298 Nm

- Ratios from 7.5:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Materials:

Casing: aluminium

Screws: treated steel 20CR


Wheel: bronze CuSn12 (cast iron hub G500)

- Lubrication: synthetic oil ISO VG320

- Weight: 8.5 kg

### Accessories

- Output shaft CHM75-X or CHM75-DX (tome 2 p.313)
- Torque arm CHM75-BR (tome 2 p.312)



### Output torque (Nm values given as a guide only)

Ratio	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	129	144	148	158	148	119	168	146	144	129
SPEED (rpm)	1400	184	194	198	209	198	159	228	209	198	188
	900	214	228	234	234	214	174	258	218	209	198
	500	258	268	278	284	254	198	298	248	238	214

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock	Price each
CHMR75-7	7,5:1	2800	373,33	NC	no	✓	422,02 €
CHMR75-10	10:1	2800	280,00	NC	no	✓	422,02 €
CHMR75-15	15:1	2800	186,66	NC	no	-	422,02 €
CHMR75-20	20:1	2800	140,00	NC	no	✓	422,02 €
CHMR75-25	25:1	2800	112,00	NC	no	-	422,02 €
CHMR75-30	30:1	2800	93,33	NC	no	✓	422,02 €
CHMR75-40	40:1	2800	70,00	NC	no	✓	422,02 €
CHMR75-50	50:1	2800	56,00	NC	not defined	-	422,02 €
CHMR75-60	60:1	2800	46,66	NC	not defined	✓	422,02 €
CHMR75-80	80:1	2800	35,00	NC	not defined	✓	422,02 €
CHMR75-100	100:1	2800	28,00	NC	yes	✓	422,02 €

\*Depending on availability - Dimensions in mm




# Worm and wheel gearbox

**Torque up to 298 Nm**


**CHM75**

- Ratios from 7.5:1 to 100:1
- With B14 flange acc IEC80 for ratios 7.5:1 to 15:1
- With B14 mounting flange acc IEC71 for ratios 20:1 to 30:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR75
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G50)
- Lubrication: synthetic oil ISO VG320
- Weight: 8.5 kg



## Accessories

- Output shaft CHM75-X or CHM75-DX (tome 2 p.313)
- Torque arm CHM75-BR (tome 2 p.312)



## Output torque (Nm values given as a guide only)

Ratio	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	129	144	148	158	148	119	168	146	144	129
SPEED (rpm)	1400	184	194	198	209	198	159	228	209	198	188
	900	214	228	234	234	214	174	258	218	209	198
	500	258	268	278	284	254	198	298	248	238	214

## DISCOUNTS

Qty	1+	2+	4+
Disc. List	-20%	-20%	On request

Part number	Ratio	Input flange	ØD	ØC	ØP	ØE	Static self-locking output	Stock*	Price each
CHM75-7	7,5:1	90B14	24	95	115	140	no	-	422,02 €
CHM75-10	10:1	90B14	24	95	115	140	no	-	422,02 €
CHM75-15	15:1	90B14	24	95	115	140	no	-	422,02 €
CHM75-20	20:1	80B14	19	80	100	120	no	-	422,02 €
CHM75-25	25:1	80B14	19	80	100	120	no	✓	422,02 €
CHM75-30	30:1	80B14	19	80	100	120	no	-	422,02 €
CHM75-40	40:1	80B14	19	80	100	120	no	-	422,02 €
CHM75-50	50:1	80B14	19	80	100	120	not defined	✓	422,02 €
CHM75-60	60:1	80B14	19	80	100	120	not defined	-	422,02 €
CHM75-80	80:1	80B14	19	80	100	120	not defined	-	422,02 €
CHM75-100	100:1	80B14	19	80	100	120	yes	✓	422,02 €

\*Depending on availability - Dimensions in mm

# Worm and wheel gearbox



## CHMR90


## Torque up to 540 Nm

- Ratios from 7.5:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G500)
- Lubrication: synthetic oil ISO VG320
- Weight: 12 kg



### Accessories

- Output shaft **CHM90-X** or **CHM90-DX** (tome 2 p.313)
- Torque arm **CHM90-BR** (tome 2 p.312)



Output torque (Nm values given as a guide only)

Ratio	7,5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	208	234	258	258	248	308	274	264	244	224
SPEED (rpm)	1400	288	308	358	354	338	408	358	338	318	284
	900	338	368	418	388	368	458	408	388	346	314
	500	408	434	438	468	438	540	478	448	398	364

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Stock*	Price each
CHMR90-7	7,5:1	2800	373,33	NC	No	-	550,77 €
CHMR90-10	10:1	2800	280,00	NC	No	✓	550,77 €
CHMR90-15	15:1	2800	186,66	NC	No	-	550,77 €
CHMR90-20	20:1	2800	140,00	NC	No	-	550,77 €
CHMR90-25	25:1	2800	112,00	NC	No	-	550,77 €
CHMR90-30	30:1	2800	93,33	NC	No	✓	550,77 €
CHMR90-40	40:1	2800	70,00	NC	No	✓	550,77 €
CHMR90-50	50:1	2800	56,00	NC	No	✓	550,77 €
CHMR90-60	60:1	2800	46,66	NC	not defined	✓	550,77 €
CHMR90-80	80:1	2800	35,00	NC	not defined	✓	550,77 €
CHMR90-100	100:1	2800	28,00	NC	Yes	✓	550,77 €

\*Depending on availability - Dimensions in mm



# Worm and wheel gearbox

**Torque up to 540 Nm**


**CHM90**

- Ratios from 7.5:1 to 100:1
- With B14 flange acc IEC90 for ratios 7.5:1 to 60:1
- With B14 mounting flange acc IEC71 for ratios 80:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR90
- Materials:
  - Casing: aluminium
  - Screws: treated steel 20CR
  - Wheel: bronze CuSn12 (cast iron hub G500)
- Lubrication: synthetic oil ISO VG320
- Weight: 3.5 kg



## Accessories

- Output shaft CHM90-X or CHM90-DX (tome 2 p.313)
- Torque arm CHM90-BR (tome 2 p.312)



## Output torque (Nm values given as a guide only)

Ratio	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	208	234	258	258	248	308	274	264	244	224
SPEED (rpm)	900	338	368	418	388	368	458	408	388	346	278
	500	408	434	438	468	438	540	478	448	398	328

## DISCOUNTS

Qty	1+	2+	4+
Disc. List	-20%	-20%	On request

Part number	Ratio	Input flange	ØD	ØC	ØP	ØE	Static self-locking output	Stock*	Price each
CHM90-7	7,5:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-10	10:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-15	15:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-20	20:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-25	25:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-30	30:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-40	40:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-50	50:1	90B5	24	130	165	200	No	-	550,77 €
CHM90-60	60:1	90B5	24	130	165	200	not defined	-	550,77 €
CHM90-80	80:1	80B5	19	130	165	200	not defined	-	550,77 €
CHM90-100	100:1	80B5	19	130	165	200	Yes	✓	550,77 €

\*Depending on availability - Dimensions in mm

# Worm and wheel gearbox



## CHMR110

## Torque up to 980 Nm

- Ratios from 7.5:1 to 100:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Materials:

Casing: cast iron

Screws: treated steel 20CR

Wheel: bronze CuSn12 (cast iron hub G500)

- Lubrication: synthetic oil ISO VG320

- Weight: 35 kg


### Info.

- See technical pages



### Accessories

- Output shaft CHM110-X or CHM110-DX (tome 2 p.313)
- Torque arm CHM110-BR (tome 2 p.312)



### Output torque (Nm values given as a guide only)

Ratio	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	100:1
INPUT	2800	380	430	480	475	490	540	520	490	465	380
SPEED (rpm)	1400	540	580	650	635	660	715	690	650	610	505
	900	640	705	740	720	740	830	780	740	675	550
	500	780	840	890	850	890	980	920	870	770	645

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-20%	On request

Part number	Ratio	Max. input speed (rpm)	Max output speed (rpm)	Efficiency at 900 rpm (%)	Static self-locking output	Price each
CHMR110-7	7.5:1	2800	373.33	NC	no	848,71 €
CHMR110-10	10:1	2800	280,00	NC	no	848,71 €
CHMR110-15	15:1	2800	186,66	NC	no	848,71 €
CHMR110-20	20:1	2800	140,00	NC	no	848,71 €
CHMR110-25	25:1	2800	112,00	NC	no	848,71 €
CHMR110-30	30:1	2800	93,33	NC	no	848,71 €
CHMR110-40	40:1	2800	70,00	NC	no	848,71 €
CHMR110-50	50:1	2800	56,00	NC	no	848,71 €
CHMR110-60	60:1	2800	46,66	NC	no	848,71 €
CHMR110-80	80:1	2800	35,00	NC	not defined	848,71 €
CHMR110-100	100:1	2800	28,00	NC	not defined	848,71 €

Dimensions in mm








# CHM and CHMR gearboxes

Stock

## CHM<sub>BR</sub>

## Reaction arm

- Mounts directly on the output side of CHM and CHMR gearboxes
- The mounting point of the reaction arm is equipped with a vibration proof bearing
- Material:  
Galvanised steel



### DISCOUNTS **A**

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request



### DISCOUNTS **B**

Qty	1+	2+	6+	15+
Disc.	List	-5%	-15%	On request

Part number	L	R	F	H	ØE	A	B	ØC	ØD	ØP	Weight (kg)	Price each	
												Stock	
CHM30-BR	85	15	24,0	14	8	38	138	65	7	55	0,18	✓	<b>A</b> 11,32 €
CHM40-BR	100	18	31,5	14	10	44	162	75	7	60	0,24	✓	<b>A</b> 13,29 €
CHM50-BR	100	18	38,5	14	10	50	168	85	9	70	0,27	✓	<b>A</b> 15,06 €
CHM63-BR	150	18	49,0	14	10	55	223	95	9	80	0,57	✓	<b>A</b> 20,73 €
CHM75-BR	200	30	47,5	25	20	70	300	115	9	95	1,10	✓	<b>B</b> 33,85 €
CHM90-BR	200	30	57,5	25	20	80	310	130	11	110	1,26	✓	<b>B</b> 49,09 €
CHM110-BR	250	35	62,0	30	25	100	385	165	11	130	1,92	-	<b>B</b> 65,92 €



\*Depending on availability - Dimensions in mm

- Mounts into the bores of the CHM and CHMR gear gearboxes
- Shaft steel C40



Single shaft CHM-X

UNI 6604  
DIN 6885



Double shaft CHM-DX

### DISCOUNTS <sup>Ⓐ</sup>

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

### DISCOUNTS <sup>Ⓑ</sup>

Qty	1+	2+	6+	15+
Disc.	List	-5%	-15%	On request

Part number	ØD h6	A	B	b	t1	R	L	Ød2	Weight (kg)	Stock*	Price each
<b>Single shaft</b>											
CHM30-X	14	30	32,5	5	16,0	69,5	102	M6x16	0,14	✓	Ⓐ 16,67 €
CHM40-X	18	40	43,0	6	20,5	85,0	128	M6x16	0,27	✓	Ⓐ 19,63 €
CHM50-X	25	50	53,5	8	28,0	99,5	153	M10x22	0,60	✓	Ⓐ 22,61 €
CHM63-X	25	50	53,5	8	28,0	119,5	173	M10x22	0,67	✓	Ⓐ 25,16 €
CHM75-X	28	60	63,5	8	31,0	128,5	192	M10x22	0,94	✓	Ⓐ 29,41 €
CHM90-X	35	80	84,5	10	38,0	149,5	234	M12x28	1,79	✓	Ⓑ 41,83 €
CHM110-X	42	80	84,5	12	45,0	164,5	249	M16x35	2,70	-	Ⓑ 47,34 €
<b>Double shaft</b>											
CHM30-DX	14	30	32,5	5	16,0	63,0	128	M6x16	0,16	✓	Ⓐ 22,61 €
CHM40-DX	18	40	43,0	6	20,5	78,0	164	M6x16	0,34	✓	Ⓐ 25,16 €
CHM50-DX	25	50	53,5	8	28,0	92,0	199	M10x22	0,75	✓	Ⓐ 28,08 €
CHM63-DX	25	50	53,5	8	28,0	112,0	219	M10x22	0,84	✓	Ⓐ 35,03 €
CHM75-DX	28	60	63,5	8	31,0	120,0	247	M10x22	1,20	-	Ⓑ 36,55 €
CHM90-DX	35	80	84,5	10	38,0	140,0	309	M12x28	2,50	-	Ⓑ 51,63 €
CHM110-DX	42	80	84,5	12	45,0	155,0	324	M16x35	3,44	-	Ⓑ 69,77 €

\* Depending on availability - Dimensions in mm

# CHM and CHMR gearboxes

## CHM CHMR

### Technical information

#### Maximum output load

When used with a double output shaft, the total of the combined loads should not exceed the values given in the table below


Loads are given for a speed of 10 rpm are the maximum loads that the gear reducers can accept.

- a : Gear constant  
b : Gear constant  
x : Load distance  
from shaft shoulder (mm)

Fr<sub>x</sub> : Radial load  
in position X (N)

Fr : Radial load (N)

Fa : Axial load (N)



#### Maximum output load (NB Speeds given are a guide only)

Sizes	CHM30	CHM40	CHM50	CHM63	CHM75	CHM90	CHM110
400	530	1020	1400	1830	2160	2390	3530
250	620	1200	1650	2150	2520	2800	4130
150	740	1420	1960	2540	2990	3310	4890
OUTPUT SPEED (rpm)	100	850	1620	2250	2910	3430	5600
60	1000	1920	2660	3450	4060	4500	6640
40	1150	2200	3050	3950	4650	5150	7600
25	1350	2570	3570	4620	5440	6020	8890
10	1830	3490	4840	6270	7380	8180	12000

#### Values of gear constants

Sizes	CHM30	CHM40	CHM50	CHM63	CHM75	CHM90	CHM110
a	65	84	101	120	131	162	176
b	50	64	76	95	101	122	136

#### Maximum radial input loads

#### Values of gear constants

Sizes	CHM30	CHM40	CHM50	CHM63	CHM75	CHM90	CHM110
a	86	106	129	159	192	227	266
b	76	94	114	139	167	202	236
Fr maxi.	210	350	490	700	980	1270	1700

#### For the CHM110 and CHMR110

- It is the user's responsibility to fill the housing with oil before use (approx 3l).
- The oil should be changed after 300 hours of use.

